




adorne Collection
adorne® 15A Single Tamper-Resistant Outlet, Graphite
Part No. ARTR151G10



Designed with the same commitment to style and safety as the entire adorne Collection, this device is ideal as a dedicated outlet for large or stationary appliances, or in small or narrow areas where a single plug is needed. The single outlet features "invisi-shutters" for discreet tamper-resistance that keeps children safe without compromising on style.

Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Replaces a standard outlet with ease in as little as 10 minutes.

Creates a designated outlet, ideal for use with appliances or products and devices with larger plugs.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	
Color	Graphite	Country Of Origin	China
Number of Receptacles	1	Outlet Type	Indoor, Residential, Tamper-Resistant
Application Sector	Residential/Commercial	Standard	RoHS, CSA, cULus, UL, Conforms to NEMA WD-1 and WD-6
Warranty Type	Limited Lifetime Warranty	Type	Single, Tamper-Resistant

Dimensions

Product Length US	1.33 in
-------------------	---------

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus ListingNumber	UL508
------------	-----	---------------------	-------

cULus Listed	Yes	CSA File Number	C22.2 No.42
--------------	-----	-----------------	-------------

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Connection	Wired	Amperage	15 A
------------	-------	----------	------

Current Rating	15 A	Indoor/Outdoor	Indoor
----------------	------	----------------	--------

Wattage	1875 W	NEMA Configuration Code	5-15R
---------	--------	-------------------------	-------

Mounting Type	Box	Operating Temperature	86°F
---------------	-----	-----------------------	------

Voltage	125.0 V	Connection Type	Internal Pressure Plates
---------	---------	-----------------	--------------------------

Environmental Conditions	Flammability Rating: UL 94 V2
--------------------------	-------------------------------
