



Pass and Seymour  
**LED Dimmer Bypass Adapter**  
Part No. DIMBPASS



Designed to improve dimmer performance, use this bypass module in applications where flickering or ghosting (when a low level of light is emitted even in the "off" position) occur. As an LED dimming load adapter, the module is usable with most 120V dimmers and makes for easier troubleshooting with ultra-low wattage LED lights. Can be wired into most electrical wall boxes (if neutral wire is present) or right at the light fixture.

## Features & Benefits

Improves dimmer performance with ultra-low wattage lights

Reduces flicker and ghosting

Suitable for installation in most wall boxes or at the light fixture

## Specifications

### General Info

Product Line	Pass & Seymour	Replaced by Part Number	
Color	Black	Finish	Matte
Country Of Origin	China	Application Sector	Residential/Commercial
Standard	RoHS, cULus	Warranty Type	1-Year Limited Warranty
Type	Accessory		

### Dimensions

Product Width US	0.87 in	Product Weight US	0.1 lb
Product Height US	0.55 in	Product Length US	1.42 in

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E172042	cULus Listed	Yes
---------------------	---------	--------------	-----

---

## Additional Information

---

RoHS Conformant                      Yes

---

## Technical Information

---

Frequency Rating                      60 Hz                                      Number of Wires                      2

---

Supply Voltage                          120 VAC                                      Operating Temperature                      0°-40°C

---

Connection Type                          Wired    Environmental Conditions                      0 to 90% (relative humidity, non-condensing)

---