



1-Pole Lock Switch, Back and Side-Wire, 20A 120/277V



Features & Benefits

External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.

Cam controls fast "make" and positive "break" to minimize arcing.

High strength thermoplastic polycarbonate toggle.

Locking support provides resistance to face and back body separation.

Grounding terminal is standard.

Strap nickel-plated steel with integral ground.

For covering patents, see www.legrand.us/patents.

Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.

Heavy-duty bumper pads for quiet operation.

Back body made of glass-reinforced nylon.

Oversized silver alloy contacts for long life and better heat dissipation.

Shallow design for ease of installation.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Application Sector	Industrial	Standard	UL 20

Dimensions

Product Width US	1.32 in	Product Depth US	1.073 in
Product Height US	2.375 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Contact Rating	20Amp, 120/277Vac	Closed Contact Resistance	Toggle
Amperage	20 A	Number of Poles	Single Pole
Wattage	1 W	Voltage	120.0 V
