



Wattstopper  
0-10V PIR Straight Mount Sensor, BLE, 120-277V, 40 ft Lens, Bronze  
Part No. FSP-311B-S-L7-BR



The FSP-3x1B sensors provide continuous dimming light level control based on motion and/or daylight contribution. They control 0-10 VDC LED drivers or dimming ballasts, as well as non-dimming ballasts and, with an FSP-Lx Lens, are rated for wet and cold locations. All control parameters are adjustable via the iOS or Android Sensor Configuration App capable of storing and transmitting sensor profiles. The FSP-3x1B family is available in three configurations for mounting inside a fixture, to the outside of a fixture via a 1/2" knockout, or to a pole.

## Features & Benefits

Designed for LED fixtures and rated for extreme temperatures; options for box or pole mounting

Fully adjustable high and low dimmed light levels

Hold off setpoint with automatic calibration option for convenience and added energy savings

Continuous dimming & daylight harvesting for energy efficiency and energy code compliance

Adjustable via the iOS® or Android® Sensor Configuration App

IP66 rated with choice of lenses for wet and outdoor locations, and mounting heights from 8' to 40'

Adjustable time delay and cutoff delay

## Specifications

### General Info

Product Line	Wattstopper	UPC Number	754182941445
Country Of Origin	China		

### Technical Information

Sensor Type	Daylight, Occupancy
-------------	---------------------