

400A 600V M PLUG ORANGE #2-2/0



Features & Benefits

Thermoplastic elastomer housing for outstanding impact and chemical resistance, as well as an exceptional seal for maintaining NEMA Type 3R and 4 integrity. Non-conductive retaining screw helps to insure no contact with live parts, along with providing stability to the fully assembled product. Heavy-duty brass male and female contacts provide a superior and consistent means of conductivity. Heavy-duty hex set screws allow greater termination torque. Copper wire provides quality strain relief. Copper shim bundles wire strands to reduce "splaying."

Specifications

General Info

Product Line	Pass & Seymour	Color	Blue
Country Of Origin	Mexico	Application Sector	Commercial/Industrial
Standard	UL, cCSAus		

Technical Information

Amperage	400 A	Number of Poles	Single Pole
Wire Size	2/0	Voltage	600.0 V

Environmental Conditions	Operating Temperature: Maximum continuous +75°C, minimum -40°C without impact: Flammability UL94 V2: Enclosure: NEMA Type 3R and 4
--------------------------	--