

# Pass and Seymour Industrial Extra Heavy Duty Specification Grade Switch, Ivory Part No. PS20AC1I



1-Pole Toggle Switch, Back and Side-Wire, 20A 120/277V

## Features & Benefits

One-piece toggle molded from chemical-,impact-,and heat-resistant thermoplastic.

Glass-reinforced, chemical-resistant thermoplastic back body for durability, strength, and resistance to harsh cleaners.

Auto-ground clip assures positive ground.

Heavy-duty bumpers for quiet, smooth operation.

Oversized silver-alloy contacts for long life and better heat dissipation.

Heavy-duty, brass alloy, one-piece contact arm virtually eliminates contact bounce.

Shallow design for easier installation.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

Impact- and chemical-resistant cover.

One-piece nickel-plated brass strap for superior corrosion-resistance.

Cam control and spring actuator for positive "makes and breaks."

Locking support provides resistance to face and back body separation.

Side and external screw-pressure-plate back wire with #14 - #10 AWG copper or copper-clad wire.

Grounding terminal is standard with screwpressure plate back wire.

For covering patents, see www.legrand.us/patents.

## **Specifications**

### General Info

Product Line	Pass & Seymour	Color	lvory
Country Of Origin	Mexico	Application Sector	Industrial
Standard	UL 498/20		

### **Dimensions**

Product Width US	1.32 in	Product Depth US	1.073 in	
Product Height US	3.281 in			
Listing Agencies / 3rd Party Agencies				
cULus ListingNumber	140597	cULus Listed	Yes	
Technical Information				
Actuator	Toggle	Contact Rating	20Amp, 120/277Vac	
Amperage	20 A	Action	Single Pole	
Number of Poles	Single Pole	Voltage	120.0 V	