



4-Way Toggle Switch, Back and Side-Wire, 20A 120/277V

Features & Benefits

External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.

Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.

Cam controls fast "make" and positive "break" to minimize arcing.

Heavy-duty bumper pads for quiet operation.

High strength thermoplastic polycarbonate toggle.

Back body made of glass-reinforced nylon.

Locking support provides resistance to face and back body separation.

Oversized silver alloy contacts for long life and better heat dissipation.

Grounding terminal is standard.

Shallow design for ease of installation.

Strap nickel-plated steel with integral ground.

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Specifications

General Info

| | | | |
|-------------------|----------------|--------------------|------------|
| Product Line | Pass & Seymour | Color | Brown |
| Country Of Origin | Mexico | Application Sector | Industrial |
| Standard | UL 20 | | |

Dimensions

| | | | |
|------------------|---------|------------------|----------|
| Product Width US | 1.32 in | Product Depth US | 1.073 in |
|------------------|---------|------------------|----------|

| | |
|-------------------|----------|
| Product Height US | 3.281 in |
|-------------------|----------|

Listing Agencies / 3rd Party Agencies

| | | | |
|------------|-----|--------------|-----|
| CSA Listed | Yes | cULus Listed | Yes |
|------------|-----|--------------|-----|

Technical Information

| | | | |
|----------------|-------------------|---------------------------|--------|
| Contact Rating | 20Amp, 120/277Vac | Closed Contact Resistance | Toggle |
|----------------|-------------------|---------------------------|--------|

| | | | |
|----------|------|-----------------|-------|
| Amperage | 20 A | Number of Poles | 4-Way |
|----------|------|-----------------|-------|

| | | | |
|---------|-----|---------|---------|
| Wattage | 4 W | Voltage | 120.0 V |
|---------|-----|---------|---------|
