



PlugTail® Decorator Spec Grade Receptacles, 20A, 125V PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.	No exposed terminals create a finger safe application before, during, and after installation.
Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.	Crimped and welded contacts.
Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.	Pre-stripped connector leads fasten to conductors, easier than standard pigtailed.
Auto-ground clip assures positive ground.	For covering patents, see www.legrand.us/patents .
Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact	PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	Country Of Origin	Mexico
Number of Receptacles	2	Outlet Type	Commercial, Indoor
Application Sector	Commercial	Standard	cULus UL498
Warranty Type	1-Year Limited Warranty	Type	Outlet

Dimensions

Product Width US	1.5 in	Product Depth US	0.625 in
------------------	--------	------------------	----------

Product Height US	2.75 in
-------------------	---------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Temperature Rating	-40° - 60° C
---------------------	--------------------------	--------------------	--------------

Amperage	20 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

Wire Size	12 AWG	Indoor/Outdoor	Indoor
-----------	--------	----------------	--------

Voltage	125.0 V
---------	---------
