



Pass and Seymour  
20A 125V Commercial Grade Tamper-Resistant Duplex Receptacle, Gray  
Part No. TR20GRY



Tamper-Resistant Commercial Grade Receptacle, 20A, 125V. Available in 6 colors. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

## Features & Benefits

Dual mechanical shutter system to help prevent insertions of foreign objects. Auto-ground clip assures positive ground.

Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring. Backed-out tri-drive steel terminal screws. Side wire only.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +50°C, minimum -40°C without impact

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Gray
Finish	Matte	Country Of Origin	Mexico
Number of Receptacles	2	Outlet Type	Commercial, Indoor, Tamper-Resistant
Application Sector	Commercial	Standard	cULus UL498, CSA C22.2 No. 42
Warranty Type	1-Year Limited Warranty	Type	Outlet

### Dimensions

Product Width US	1.37 in	Product Depth US	0.93 in
------------------	---------	------------------	---------

---

Product Height US	3.28 in
-------------------	---------

---

### Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

---

### Technical Information

---

Dielectric Strength	Withstands 1500V minimum	Is Tamper-Resistant	Yes
---------------------	--------------------------	---------------------	-----

---

Temperature Rating	-40° - 50° C	Amperage	20 A
--------------------	--------------	----------	------

---

Number of Poles	Double Pole	Wire Size	14 - 10 AWG
-----------------	-------------	-----------	-------------

---

Indoor/Outdoor	Indoor	Voltage	125.0 V
----------------	--------	---------	---------

---