

# Pass and Sevmour Fed Spec Grade USB Charger with Tamper-Resistant Duplex Receptacles, Nickel Part No. TR5262USBNI



Designed for commercial markets with strength and durability in mind, this combination USB charger duplex receptacle features 3.1A overall USB charging capability and is compatible with USB 2.0 and 3.0 devices. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

## Features & Benefits

Overall 3.1A USB charging capability: Combination AC duplex receptacles include two 5volt DC USB ports that work with USB 2.0 & 3.0 compatible devices.

AC receptacles available in 15 and 20A, 125V.

AC receptacles are tamper-resistant as standard: patented shutter system prevents improper insertion of foreign objects.

Multiple color options available.

Back and side wire terminals accommodate #14 AWG - #10 AWG stranded and solid copper Stainless steel auto-ground clips wire. assure positive ground.

For covering patents, see www.legrand.us/patents.

Wire Size: #14 - #10 AWG Copper Conductor Only

# Specifications

### General Info

China	Application Sector	Commercial
CSA Listed, cULus, FSUL, UL Listed, RoHS		
	CSA Listed, cULus, FSUL, UL	CSA Listed, cULus, FSUL, UL

Product Width US	1.693 in	Product Depth US	1.392 in
Product Height US	2.677 in		

# Listing Agencies / 3rd Party Agencies

cULus Listed	Yes		
Additional Information			
Product Environmental Profile	Yes		
Technical Information			
Dielectric Strength	Withstands 2000V minimum	Is Tamper-Resistant	Yes
USB Amperage	3.1 A	Phase	Single
Connection	Side & Back Wired	Number of USBs	2
Number of Wires	3	USB Power Output	15 W
Temperature Rating	-40° - 60° C	Amperage	15 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Voltage	125.0 V	Environmental Conditions	UL94 V2