



Tamper-Resistant Hospital Grade Receptacles, Back and Side Wire, 20A, 125V

Features & Benefits

- Thermoplastic dual mechanism shutter system to help prevent insertion of foreign objects. AC receptacles available in 15 and 20 Amp, 125V
- Extra heavy-duty brass, one-piece mounting strap with integral ground. One-piece, nickel-plated: brass, triple-wipe power contacts for lasting retention.
- Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body. Impact-resistant nylon face and back body.
- Two drive screws anchor strap to back body and face. Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.
- External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection. Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	Country Of Origin	Mexico
Number of Receptacles	2	Outlet Type	Commercial, Indoor, Tamper-Resistant
Application Sector	Commercial	Standard	UL498, CSA C22.2 No. 42
Type	Outlet		

Dimensions

Product Width US	1.625 in	Product Depth US	0.9 in
Product Height US	2.75 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Is Tamper-Resistant	Yes
Temperature Rating	-40° - 60° C	Amperage	20 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Indoor/Outdoor	Indoor	Voltage	125.0 V
