



Pass and Seymour

20A 125V Construction Spec-Grade Tamper-Resistant Single Receptacle, Back and Side Wire, Ivory

Part No. TR5351I

Tamper-Resistant Construction Spec Grade Single Receptacles, Back and Side Wire, 20A, 125V



Features & Benefits

Dual mechanical shutter system to help prevent insertions of foreign objects. AC receptacles available in 15 and 20A, 125V.

.032 inch thick brass triple-wipe power contacts for lasting retention.

Corrosion-resistant plated steel strap is locked in to the face and back body to resist pulling away from the face/body assembly.

Auto-ground clip assures positive ground.

Easily accessed break-off line-contact connecting tab for fast and easy split-circuitwiring.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.

Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	Mexico	Number of Receptacles	1
Outlet Type	Commercial, Indoor, Tamper-Resistant	Application Sector	Commercial
Standard	UL498, CSA C22.2 No. 42	Warranty Type	1-Year Limited Warranty

Type	Outlet
------	--------

Dimensions

Product Width US	1.38 in	Product Depth US	1.19 in
------------------	---------	------------------	---------

Product Height US	3.28 in
-------------------	---------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Is Tamper-Resistant	Yes
---------------------	--------------------------	---------------------	-----

Connection	Back and side wire	Number of Wires	3
------------	--------------------	-----------------	---

Temperature Rating	-40° - 60° C	Amperage	20 A
--------------------	--------------	----------	------

Number of Poles	Double Pole	Wire Size	14 - 10 AWG
-----------------	-------------	-----------	-------------

Indoor/Outdoor	Indoor	Voltage	125.0 V
----------------	--------	---------	---------

Environmental Conditions	Flammability: UL94 V2
--------------------------	-----------------------
