

Pass and Seymour Weather-Resistant Heavy Duty Spec Grade Receptacles, Back and Side Wire, 20A, 125V, Gray Part No. WR5362GRY



Weather-Resistant Heavy-Duty Spec Grade Duplex Receptacle Back and Side-Wire 20A 125V

Features & Benefits

Auto-ground clip assures positive ground.

Zinc-plated steel mounting screws for greater ease of installation and removal in wet or damp locations.

Tri-drive brass terminal screws.

Two back wire holes for more wiring flexibility.

UV-resistant nylon face for longer life under adverse environmental conditions

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

For covering patents, see www.legrand.us/patents.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

WR marking on face as required by UL Standard.

Strap tabs wrap around face to prevent strap from separating from face and back body.

Internal screw-pressure-plate back and side wire capability.

Heavy-duty, brass strap for added strength and ground conductivity.

Two drive screws anchor strap to back body and face where abrupt removal torque is strongest.

.032 inch thick brass triple-wipe power contacts for lasting retention.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Country Of Origin	United States	Application Sector	Commercial

Standard	UL 498				
Dimensions					
Product Width US	1.322 in	Product Depth US	0.78 in		
Product Height US	2.635 in				
Listing Agencies / 3rd Party Agencies					
cULus ListingNumber	140596	cULus Listed	Yes		
Technical Information					
Phase	Three	Number of Wires	3		
Amperage	20 A	Number of Poles	Double Pole		
Wire Size	14 - 10 AWG	Voltage	125.0 V		