GW100 Gateway.

System Information

LAN Connection 5 LAN - RJ45 - 10/100/1000 Mbps Wireless Connection 2 TX x 2 RX MIMO, IEEE 802.11a/b/g/n

Dual Band - Concurrent

Wireless Data Rate Up to 300 Mbps

Power Requirements

Power Supply 12V DC, 1.0A Input Voltage 100-240VAC, 50/60 Hz

Rated Power 12 W

Regulatory Approvals

Controller

EMC FCC, IC, CE-EMC, C-Tick

Power Supply

Safety cULus, GS Mark, CE-LVD EMC FCC, IC, CE-EMC, C-Tick Environmental Compliance Europe RoHS

Operating Temperature

Specifications

0° C to 40° C

Physical Specifications

Unit Size (mm) 112.5 H x 177 W x 133 D (including antennas)
Unit Size (inch) 4.82 H x 6.97 W x 5.24 D (including antennas)
Unit Weight (kg) 0.30
Unit Weight (lbs) 0.65

Shipping Specifications

 Unit Size (mm)
 240 L x 230 W x 66 H

 Unit Size (inch)
 9.45 L x 9.06 W x 2.60 H

 Unit Weight (kg)
 0.975

 Unit Weight (pounds)
 2.15

NuVo reserves the right to change specifications without notice.

Office Toll Free: 866.796.4904
Office Direct: 859.817.7200
Email: sales@nuvotechnologies.com
Web: www.nuvotechnologies.com