

Ortronics 2 Meters (2 m), 4 Duplex LC/UPC To accIAIM/UPC, 9/125 OS2 Single-Mode, ONFP Plenum, 8 Fiber, Distribution Harness Cable, Yellow



The 4 Duplex LC to acclAIM, 8 Fiber, Distribution Harness Cable, is designed to interface acclAIM adapter panels and breakout to individual Duplex LC connectors to interface active equipment or other patch panels within Network Racks, or in top of rack configurations. The acclAIM breakout cable is also a great solution for Telco Rooms, Meet Me Rooms, IDFs, Carrier rooms, Demarcations, and more as a cost-effective less time-consuming alternative to field termination.

Features & Benefits

- Catalog & Belletits			
Part of an acclAIM Connectivity Solution: Typical total channel loss of $0.4\mathrm{dB}$ TIA Channel Compliant		Bend-insensitive fiber for optimal cable management and ease of installation Dust caps pre-installed	
General Info			
Product Line	Ortronics	Color	Yellow
Country Of Origin	United States		
Dimensions			
Product Weight US	0.08 lb	Product Length US	2.0 m
Technical Information			
Fiber Optic Cable Type	0S2	Jacket Application	Plenum Rated
Minimum Insertion Loss	55 dB	Number of Fanout Cables	4
Jacket Rating	Plenum OFNP-Rated	Fanout Cable Diameter	2 mm
Connector Type	Infinium acclAIM	Fanout Cable Length	24 in
Wavelength	1550 nm, 1310 nm	Operating Temperature	32°-158°F
Fiber Size	9/125	Maximum Insertion Loss	0.3 dB
Storage Temperature	-40° - 158° F		