

## Pass and Sevmour TurnLok® 50A California Style 480V 2-Pole 3-Wire Locking Plug Part No. CS8465C



50A Turnlok Plugs and Connectors make installing and securing your connections faster, safer and more dependable than ever. These devices are designed to withstand harsh environments. Each device features a simple push, twist and lock body assembly for greater productivity and labor savings in temporary power applications. The back body easily slides onto the device and locks in place with a quarter twist making installations faster, safer and more dependable.

## Features & Benefits

Securing your installations is easier than ever. The back body easily body for greater flexibility to accommodate a wider slides onto the device and locks in place with a simple quarter twist. range of cord sizes. Clamp screws are on the same No time-consuming threading.

An adjustable cord clamp is located outside the back plane for faster installation. Longer screws are included to adjust for larger cables.

Same-plane hex head terminations for faster, easier and safer terminations that allow more torque to be applied without the risk of Industrial-strength, brass alloy plug blades and harmful screwdriver slips. All termination screws are on the same plane for a more accurate and streamlined installation that saves you precious time on the job.

connector contacts resist heat rise and provide excellent conductivity.

Impact- and corrosion-resistant durable nylon 66 shell material.

Visible molded NEMA configuration and device rating.

Newly designed external cord grips provide visible assurance of safe and proper cord retention.

Integral flexible rubber cord gromet conforms to and seals around SO cord to provide protection from oils, water or chips entering wiring chamber.

## Specifications

## General Info Product Line Pass & Seymour Black Color Country Of Origin Mexico **Application Sector** Commercial/Industrial Standard RoHS, UL UL498, cULus E146159 Locking Plug Type **Dimensions** Product Width US 2.48 in 2.48 in Product Height US

Product Length US 6.39 in			
Listing Agencies / 3rd Party Agencies			
cULus Listed	Yes		
Additional Information			
RoHS Conformant	Yes		
Technical Information			
Number of Wires	3	Contact Material	Brass
Amperage	50 A	Voltage	480.0 V