




Ortronics  
10 Meters (10 m), 4 Duplex LC/UPC To acclAIM/UPC, 9/125 OS2 Single-Mode, ONFP Plenum, 8 Fiber, Distribution Harness Cable, Yellow  
Part No. C80AM137S5JEM0010M



The 4 Duplex LC to acclAIM, 8 Fiber, Distribution Harness Cable, is designed to interface acclAIM adapter panels and breakout to individual Duplex LC connectors to interface active equipment or other patch panels within Network Racks, or in top of rack configurations. The acclAIM breakout cable is also a great solution for Telco Rooms, Meet Me Rooms, IDFs, Carrier rooms, Demarcations, and more as a cost-effective less time-consuming alternative to field termination.

## Features & Benefits

Part of an acclAIM Connectivity Solution: Typical total channel loss of 0.4 dB

Bend-insensitive fiber for optimal cable management and ease of installation

TIA Channel Compliant

Dust caps pre-installed

## Specifications

### General Info

Product Line	Ortronics	Color	Yellow
Country Of Origin	United States		

### Dimensions

Product Weight US	0.39 lb	Product Length US	10.0 in
-------------------	---------	-------------------	---------

### Technical Information

Fiber Optic Cable Type	OS2	Jacket Application	Plenum Rated
Minimum Insertion Loss	55 dB	Number of Fanout Cables	4
Jacket Rating	Riser OFNR-Rated	Fanout Cable Diameter	2 mm
Fanout Cable Length	24 in	Wavelength	1310 nm, 1550 nm
Operating Temperature	32°-158°F	Fiber Size	9/125
Maximum Insertion Loss	0.3 dB		