



Pass and Seymour  
20A 125V Heavy Duty Hospital-Grade Smooth Face Duplex Receptacle, Back and Side Wire, Red  
Part No. PS8300HSRED



Heavy-Duty Hospital Grade Smooth Face Duplex Receptacle Back and Side Wire 20A 125V

## Features & Benefits

Heavy-duty, brass strap for added strength and ground conductivity.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Tri-drive brass terminal screws.

Auto-ground clip assures positive ground.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Strap tabs wrap around face to prevent strap from separating from face and back body.

Two drive screws anchor strap to back body and face.

Two back wire holes for more wiring flexibility.

Smooth face version features an impact-resistant nylon face for ease of cleaning and less dirt build-up.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Red
Country Of Origin	United States	Number of Receptacles	2
Outlet Type	Commercial, Indoor	Application Sector	Commercial
Standard	UL498, CSA C22.2 No. 42	Type	Outlet

### Dimensions

---

Product Width US 1.322 in

Product Depth US 1.018 in

---

Product Height US 2.635 in

---

### Listing Agencies / 3rd Party Agencies

---

cULus Listed Yes

---

### Technical Information

---

Dielectric Strength Withstands 2000V minimum Connection Back and side wire

---

Number of Wires 3 Temperature Rating -40° - 60° C

---

Amperage 20 A Number of Poles Double Pole

---

Wire Size 14 - 10 AWG Indoor/Outdoor Indoor

---

Voltage 125.0 V Environmental Conditions Flammability: UL94 V2

---