



Pass and Seymour
PlugTail® 20A 125V Spec-Grade Tamper-Resistant Duplex Receptacle, Ivory
Part No. PTTR5362I



PlugTail® Tamper-Resistant Spec Grade Receptacles, 20A, 125V
PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

Smooth wall plate.

No exposed terminals create a finger safe application before, during, and after installation.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Crimped and welded contacts.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

Pre-wired with one welded pre-stripped wire lead to facilitate switched receptacle circuit applications.

Auto-ground clip assures positive ground.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	Mexico	Number of Receptacles	2
Outlet Type	Commercial, Indoor, Tamper-Resistant	Application Sector	Commercial

Standard	cULus UL498	Warranty Type	1-Year Limited Warranty
Type	Outlet		
Dimensions			
Product Width US	1.5 in	Product Depth US	0.625 in
Product Height US	2.75 in		
Listing Agencies / 3rd Party Agencies			
cULus Listed	Yes		
Technical Information			
Dielectric Strength	Withstands 2000V minimum	Is Tamper-Resistant	Yes
Number of Wires	3	Temperature Rating	-40° - 60° C
Amperage	20 A	Number of Poles	Double Pole
Wire Size	12 AWG	Indoor/Outdoor	Indoor
Voltage	125.0 V	Environmental Conditions	Flammability: UL94 V2