



Tamper-Resistant Hospital Grade Receptacles, Smooth Face, Back and Side-Wire, 15A, 125A

## Features & Benefits

Thermoplastic dual mechanism shutter system to help prevent insertion of foreign objects.

Exclusive patented feature, circuit label on face allows permanent circuit identification.

One-piece, nickel-plated brass, triple-wipe power contacts for lasting retention.

Impact-resistant nylon face and back body.

Two drive screws anchor strap to back body and face.

External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.  
Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Smooth face.

Extra heavy-duty brass, one-piece mounting strap with integral ground.

Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Brown
--------------	----------------	-------	-------

Country Of Origin	Mexico	Application Sector	Commercial
Standard	UL 498		
Dimensions			
Product Width US	1.625 in	Product Depth US	0.9 in
Product Height US	2.75 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	140596	cULus Listed	Yes
Technical Information			
Is Tamper-Resistant	Yes	Phase	3
Number of Wires	3	Amperage	15 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Voltage	125.0 V		