






LD and SB



VC and SC



WIDTH W	RADIUS R	H=4		H=5		H=6		H=7	
		A	B	A	B	A	B	A	B
ALL	12	13 5/8	3 5/8	14 1/8	3 3/4	14 5/8	3 7/8	15 1/8	4
	24	19 5/8	5 1/4	20 1/8	5 3/8	20 5/8	5 1/2	21 1/8	5 5/8
	36	25 5/8	6 7/8	26 1/8	7	26 5/8	7 1/8	27 1/8	7 1/4

- **Material:** Aluminum Alloy 6063 and 5052
- **Finish:** Plain
- **Bottom:** LD: 1" wide rung

SB: Flat sheet over Rung
SC: Solid Corrugated
VC: Vented Corrugated

- **Construction:** Welded
- **Tray Design:** Tray construction and markings are per the latest edition of NEMA Standards Publication VE1, CSA C22.2 No. 126
- **Connectors:** All fittings are supplied with necessary connectors and fasteners
- **Fitting heights (H):** 4", 5", 6", 7"

ITRAY VERTICAL INSIDE ELBOW CATALOG NUMBERING EXAMPLE:					
BOTTOM TYPE	LD - 4	A	- 30VI	12 - 09	WIDTH
VENTED	LD - Ladder Rung	RAIL HEIGHT	FITTING CODE	RADIUS	06 - 6"
VC - Vented Corrugated	4 - 4"	5 - 5"	12 - 12"	18 - 18"	09 - 9"
NON-VENTED	5 - 5"	6 - 6"	24 - 24"	30 - 30"	12 - 12"
SC - Solid Corrugated	6 - 6"	7 - 7"	36 - 36"		18 - 18"
SB - Solid Bottom	7 - 7"				24 - 24"
					30 - 30"
					36 - 36"