



FTEC 50 shown



Hardware included

- M6x12mm square neck carriage bolt (zinc plated)
- M6 serrated flange hex nut (zinc plated)

	PACK	HEIGHT		PG	BL	YL	OR
	PCS	INCHES	MM	STANDARD		OPTIONAL	
FTEC 50	50	2	50	341 561	960 015	960 371	960 194
FTEC 100	50	4	100	341 674	960 018	960 374	960 197

All dimensions are nominal.

FINISHES			
SYMBOL	MATERIAL		FINISH & STANDARD
STANDARD	PG	Carbon Steel	Pre-Galvanized: Continuous Galvanization Before Fabrication ASTM A 653
	BL	Carbon Steel ASTM A510 Grade 1008	Black Painted: Black Powder Coated ASTM D 3451
OPTIONAL	YL	Carbon Steel ASTM A510 Grade 1008	Yellow Painted: Yellow Powder Coated ASTM D 3451
	OR	Carbon Steel ASTM A510 Grade 1008	Orange Painted: Orange Powder Coated ASTM D 3451

Legrand/Cablofil
 8319 State Route 4
 Mascoutah, IL 62258 USA
 1-800-658-4641
 618-566-3230
 Fax 618-566-3250
www.legrand.us/cablofil