

legrand® | Cablofil

PW Cable Tray


TRAY SYSTEM NUMBER **3734RS**




RAIL CROSS SECTION



RUNG CROSS SECTION



CONNECTOR



AISI Type 304L **L**

GENERAL INFORMATION

NEMA TRAY TYPE: Two Rail Ladder
NEMA CLASS: 12B
MATERIAL: AISI Type 304L Stainless Steel
SIDE RAIL: 7" high with 1" top flange
LOAD DEPTH: 6"
BOTTOM: 1 1/4" wide hat rung
FINISH: Plain
CONSTRUCTION: Resistance welded
TRAY SERIES: Series 1 (2" tangent)

ENGINEERING INFORMATION

TRAY DESIGN: Construction and markings are per the latest edition of NEMA Standards Pub. VE1.

TRAY GROUNDING CAPABILITY: None. The N.E.C. does not recognize stainless steel cable tray as an equipment ground conductor.

CONNECTORS: Supplied in pairs with hardware. Splice resistance is less than 0.00033 ohms. Standard hardware: 3/8 in. type 316 stainless steel.

MECHANICAL PROPERTIES:
One rail: I x-x = 2.5243in^3 S x-x = 0.7830in^4

TRAY WIDTH (IN.)	TRAY WEIGHT* (LBS./FT.)
6	3.50
9	3.67
12	3.84
18	4.18
24	4.52
30	5.38
36	5.83

Based on 9" rung spacing

SAFE LOAD DATA (LBS./FT.) / **SUPPORT SPAN** (FT.) / **DEFLECTION** (IN.)

6		8		10		12		14		16		18		20		22		24		26		28		30	
300	0.10	169	0.17	108	0.27	75	0.39																		

CATALOG NUMBERING EXAMPLE:

09 - 3734 - 0012 - 36

Bottom Type
06 – 6" Rung Spacing
09 – 9" Rung Spacing*
12 – 12" Rung Spacing
18 – 18" Rung Spacing
** Standard rung spacing*

Tray System Number

Length
0010 – 10'-0"
0012* – 12'-0"
0020 – 20'-0"
0024 – 24'-0"
** Standard for Series 1*

Width
06 – 6"
09 – 9"
12 – 12"
18 – 18"
24 – 24"
30 – 30"
36 – 36"


Legrand/Cablofil
Phone 800-658-4641
618-566-3230
Fax 618-566-3250
8319 State Route 4
Mascoutah, IL 62258 USA


Publication Date: 3/10
Copyright © 2010 Legrand/Cablofil


legrand® | Cablofil

PW Cable Tray

TRAY SYSTEM NUMBER **3734SF**







AISI Type 304L **L**

GENERAL INFORMATION

NEMA TRAY TYPE: Solid Flat
NEMA CLASS: 12B
MATERIAL: AISI Type 304L Stainless Steel
SIDE RAIL: 7" high with 1" top flange
LOAD DEPTH: 6"
BOTTOM: Solid Flat
FINISH: Plain
CONSTRUCTION: Arc welded
TRAY SERIES: Series 1 (2" tangent)

ENGINEERING INFORMATION

TRAY DESIGN: Construction and markings are per the latest edition of NEMA Standards Pub. VE1.

TRAY GROUNDING CAPABILITY: None. The N.E.C. does not recognize stainless steel cable tray as an equipment ground conductor.

CONNECTORS: Supplied in pairs with hardware. Splice resistance is less than 0.00033 ohms. Standard hardware: 3/8 in. type 316 stainless steel.

MECHANICAL PROPERTIES:
One rail: I x-x = 2.5243in^3 S x-x = 0.7830in^4

TRAY WIDTH (IN.)	TRAY WEIGHT (LBS./FT.)
6	4.17
9	4.67
12	5.18
18	6.19
24	7.20
30	8.20
36	9.46

SAFE LOAD DATA (LBS./FT.) / **SUPPORT SPAN** (FT.) / **DEFLECTION** (IN.)

6		8		10		12		14		16		18		20		22		24		26		28		30	
300	0.10	169	0.17	108	0.27	75	0.39																		

CATALOG NUMBERING EXAMPLE:

SF-3734-0012-36

Bottom Type
SF – Solid Flat

Tray System Number

Length
0010 – 10'-0"
0012* – 12'-0"
0020 – 20'-0"
0024 – 24'-0"
** Standard for Series 1*

Width
06 – 6"
09 – 9"
12 – 12"
18 – 18"
24 – 24"
30 – 30"
36 – 36"

Legrand/Cablofil
Phone 800-658-4641
618-566-3230
Fax 618-566-3250
8319 State Route 4
Mascoutah, IL 62258 USA

Publication Date: 3/10
Copyright © 2010 Legrand/Cablofil