


AISI Type 316L

T

GENERAL INFORMATION

NEMA TRAY TYPE:	Two Rail Ladder
NEMA CLASS:	20C
MATERIAL:	AISI Type 316L Stainless Steel
SIDE RAIL:	7" high with 1 3/4" top flange
LOAD DEPTH:	6"
BOTTOM:	1" wide box rung
FINISH:	Plain
CONSTRUCTION:	Arc welded
TRAY SERIES:	Series 2 (5" tangent)

ENGINEERING INFORMATION

TRAY DESIGN: Construction and markings are per the latest edition of NEMA Standards Pub. VE1.

TRAY GROUNDING CAPABILITY: None. The N.E.C. does not recognize stainless steel cable tray as an equipment ground conductor.

CONNECTORS: Supplied in pairs with hardware. Splice resistance is less than 0.00033 ohms. Standard hardware: 3/8 in. type 316 stainless steel.

MECHANICAL PROPERTIES:

One rail: $I x-x = 4.9763 \text{ in}^3$ $S x-x = 1.5260 \text{ in}^4$

TRAY WIDTH (IN.)	TRAY WEIGHT* (LBS./FT.)
6	5.91
9	6.08
12	6.25
18	6.59
24	6.94
30	7.80
36	8.24

*Based on 9" rung spacing

SAFE LOAD DATA (LBS./FT.) / SUPPORT SPAN (FT.) / DEFLECTION (IN.)																									
6		8		10		12		14		16		18		20		22		24		26		28		30	
		564	0.28	400	0.48	278	0.69	204	0.93	156	1.22	123	1.55	100	1.91	81	2.05	63	2.28						

CATALOG NUMBERING EXAMPLE:

09 - 3760 - 0020 - 36			
Bottom Type	Tray System Number	Length	Width
06 - 6" Rung Spacing		0010 - 10'-0"	06 - 6"
09 - 9" Rung Spacing*		0012 - 12'-0"	09 - 9"
12 - 12" Rung Spacing		0020* - 20'-0"	12 - 12"
18 - 18" Rung Spacing		0024 - 24'-0"	18 - 18"
* Standard rung spacing		* Standard for Series 2	24 - 24"
			30 - 30"
			36 - 36"

Legrand/Cablofil

Phone 800-658-4641

618-566-3230

Fax 618-566-3250

8319 State Route 4

Mascoutah, IL 62258 USA

Publication Date: 3/10

Copyright © 2010 Legrand/Cablofil