


AISI Type 316L

T

GENERAL INFORMATION

NEMA TRAY TYPE:	Two Rail Ladder
NEMA CLASS:	12C
MATERIAL:	AISI Type 316L Stainless Steel
SIDE RAIL:	7" high with 1" top flange
LOAD DEPTH:	6"
BOTTOM:	1 1/4" wide hat rung
FINISH:	Plain
CONSTRUCTION:	Resistance welded
TRAY SERIES:	Series 1 [2" tangent]

ENGINEERING INFORMATION

TRAY DESIGN: Construction and markings are per the latest edition of NEMA Standards Pub. VE1.

TRAY GROUNDING CAPABILITY: None. The N.E.C. does not recognize stainless steel cable tray as an equipment ground conductor.

CONNECTORS: Supplied in pairs with hardware. Splice resistance is less than 0.00033 ohms. Standard hardware: 3/8 in. type 316 stainless steel.

MECHANICAL PROPERTIES:
One rail: $I_{x-x} = 2.6403 \text{ in}^3$ $S_{x-x} = 0.8411 \text{ in}^4$

TRAY WIDTH (IN.)	TRAY WEIGHT* (LBS./FT.)
6	3.68
9	3.85
12	4.02
18	4.36
24	4.70
30	5.56
36	6.01

*Based on 9" rung spacing

SAFE LOAD DATA (LBS./FT.) / SUPPORT SPAN (FT.) / DEFLECTION (IN.)												
6	8	10	12	14	16	18	20	22	24	26	28	30
400 0.11	225 0.19	144 0.30	100 0.43									

CATALOG NUMBERING EXAMPLE:

09-3739-0012-36			
Bottom Type	Tray System Number	Length	Width
06 - 6" Rung Spacing		0010 - 10'-0"	06 - 6"
09 - 9" Rung Spacing*		0012* - 12'-0"	09 - 9"
12 - 12" Rung Spacing			12 - 12"
			18 - 18"
			24 - 24"
			30 - 30"
			36 - 36"

* Standard rung spacing

* Standard for Series 1

Legrand/Cablofil

Phone 800-658-4641

618-566-3230




Fax 618-566-3250

8319 State Route 4

Mascoutah, IL 62258 USA

Publication Date: 3/10

Copyright © 2010 Legrand/Cablofil



AISI Type 316L

T

GENERAL INFORMATION

NEMA TRAY TYPE:	Solid Flat
NEMA CLASS:	12C
MATERIAL:	AISI Type 316L Stainless Steel
SIDE RAIL:	7" high with 1" top flange
LOAD DEPTH:	6"
BOTTOM:	Solid Flat
FINISH:	Plain
CONSTRUCTION:	Arc welded
TRAY SERIES:	Series 1 [2" tangent]

ENGINEERING INFORMATION

TRAY DESIGN: Construction and markings are per the latest edition of NEMA Standards Pub. VE1.

TRAY GROUNDING CAPABILITY: None. The N.E.C. does not recognize stainless steel cable tray as an equipment ground conductor.

CONNECTORS: Supplied in pairs with hardware. Splice resistance is less than 0.00033 ohms. Standard hardware: $\frac{3}{8}$ in. type 316 stainless steel.

MECHANICAL PROPERTIES:


One rail: $I_{x-x} = 2.6403 \text{ in}^3$ $S_{x-x} = 0.8411 \text{ in}^4$

TRAY WIDTH (IN.)	TRAY WEIGHT (LBS./FT.)
6	4.35
9	4.85
12	5.36
18	6.37
24	7.38
30	8.38
36	9.64

SAFE LOAD DATA (LBS./FT.) / SUPPORT SPAN (FT.) / DEFLECTION (IN.)

6	8	10	12	14	16	18	20	22	24	26	28	30
400	0.11	225	0.19	144	0.30	100	0.43					

CATALOG NUMBERING EXAMPLE:



Legrand/Cablofil

Phone 800-658-4641

618-566-3230

Fax 618-566-3250

8319 State Route 4

Mascoutah, IL 62258 USA

Publication Date: 3/10

Copyright © 2010 Legrand/Cablofil