



RX Horizontal Reducing Cross



MAIN WIDTH W1	BRANCH WIDTH W2	RADIUS R	A	B	RADIUS R	A	B	RADIUS R	A	B
9	6	12	36	39	24	60	39	36	84	87
12	6		36	42		60	42		84	90
	9		39	42		63	42		87	90
18	6		36	48		60	48		84	96
	9		39	48		63	48		87	96
	12		42	54		66	48		90	96
24	6		36	54		60	54		84	102
	9		39	54		63	54		87	102
	12		42	54		66	54		90	102
	18		48	60		72	54		96	102
30	6		36	60		60	60		84	108
	9		39	60		63	60		87	108
	12		42	60		66	60		90	108
	18		48	60		72	60		96	108
	24		54	60		78	60		102	108
36	6	24	36	66	36	60	66	48	84	114
	9		39	66		63	66		87	114
	12		42	66		66	66		90	114
	18		48	66		72	66		96	114
	24		54	66		78	66		102	114
	30		60	66		84	66		108	114

- **Material:** Aluminum Alloy 6063 and 5052
- **Finish:** Plain
- **Bottom:** LD: 1" wide rung
SB: Flat sheet over Rung
- **Construction:** Welded
- **Tray Design:** Tray construction and markings are per the latest edition of NEMA Standards Publication VE1, CSA C22.2 No. 126
- **Connectors:** All fittings are supplied with necessary connectors and fasteners
- **Fitting Heights (H):** 4", 5", 6", 7"

ITRAY HORIZONTAL REDUCING CROSS CATALOG NUMBERING EXAMPLE:									
BOTTOM TYPE		← L D - 4 A - R X 12 - 0 9 0 6 →						WIDTH 2	
VENTED		RAIL HEIGHT 4 - 4" 5 - 5" 6 - 6" 7 - 7"		FITTING CODE RX		RADIUS 12 - 12" 24 - 24" 36 - 36"		06 - 6"	
LD - Ladder Rung								09 - 9"	
NON-VENTED		MATERIAL A						12 - 12"	
SB - Solid Bottom								18 - 18"	
								24 - 24"	
								30 - 30"	
								36 - 36"	
								36 - 36"	