



RX Horizontal Reducing Cross



MAIN WIDTH W1	BRANCH WIDTH W2	RADIUS R	A	B	RADIUS R	A	B	RADIUS R	A	B
9	6	12	36	39	24	60	63	36	84	87
12	6		36	42		60	66		84	90
	9		39	42		63	66		87	90
18	6		36	48		60	72		84	96
	9		39	48		63	72		87	96
	12		42	54		66	72		90	96
24	6		36	54		60	78		84	102
	9		39	54		63	78		87	102
	12		42	54		66	78		90	102
	18		48	60		72	78		96	102
30	6		36	60		60	84		84	108
	9		39	60		63	84		87	108
	12		42	60		66	84		90	108
	18		48	60		72	84		96	108
	24		54	60		78	84		102	108
36	6		36	66		60	90		84	114
	9		39	66		63	90		87	114
	12		42	66		66	90		90	114
	18		48	66		72	90		96	114
	24		54	66		78	90		102	114
	30		60	66		84	90		108	114

- **Material:** Aluminum Alloy 6063 and 5052
- **Finish:** Plain
- **Bottom:** LD: 1" wide rung
SB: Flat sheet over Rung
- **Construction:** Welded
- **Tray Design:** Tray construction and markings are per the latest edition of NEMA Standards Publication VE1, CSA C22.2 No. 126
- **Connectors:** All fittings are supplied with necessary connectors and fasteners
- **Fitting Heights (H):** 4", 5", 6", 7"

ITRAY HORIZONTAL REDUCING CROSS CATALOG NUMBERING EXAMPLE:					
BOTTOM TYPE		LD - 4	A	RX	12-0906
VENTED					
LD - Ladder Rung					
NON-VENTED					
SB - Solid Bottom					
RAIL HEIGHT		4 - 4"	FITTING CODE RX	WIDTH 2	
		5 - 5"		06 - 6"	
		6 - 6"		09 - 9"	
		7 - 7"		12 - 12"	
			RADIUS	18 - 18"	
				24 - 24"	
				30 - 30"	
				36 - 36"	
				48 - 48"	