Essentia (NV-E6GM).

Specifications

Zones 1-6 Power Amplifier Outputs Continuous Average Output Power	40W (20W x 2)	Zone Trigger Outputs Output Power	5VDC @ 20mA
Two channels driven 30-20kHz @ 1% THD		Outputs	2 (zones 1, 2)
Rated Distortion (1/2 power)	0.40%		
Rated Impedance	6 ohm	Power Requirements	
Damping Factor	50+	Power Supply	85-265VAC 50/60Hz
Frequency Response (20-20kHz)	± 2dB	Power Consumption all channels at	
		maximum available output	150VA (150W)
Zones 1,2 Preamplifier Outputs		Power Consumption at average	
Variable Output	0-2.4V RMS	operating conditions	70VA (70W)
Fixed Output	2.4V RMS	Power Consumption no signal	18VA (12W)
Impedance	1k ohm	Standby Power	0.8W
Source Inputs 1-6		Regulatory Approvals	
Input Impedance	20K	USA Safety Listing (UL 6500)	
Input Sensitivity for Rated Power	300mV RMS	Canada Safety Listing (CAN/CSA E60065.00)	
Input Overload	2.4V RMS	CE Listing/SEMKO (EN60065, EN55013, EN55020,	
		EN6100-3-2, EN6100-3-3/A1)	
Emitter Outputs			
Source Outputs	6	Physical Specifications	
Sum Outputs	1	Unit Size (mm)	44 H x 430 W x 250 D
Output Drive	Current 20mA	Unit Size (inch)	1 3/4 H x 17 W x 9 7/8 D
Output Drive Voltage	5VDC	Unit Weight (kg)	3.0
Compatible with single and dual emitters		Unit Weight (lbs)	6.65
		Shipping Specifications	
System		Shipping Size (mm)	265 H x 558 W x 375 D
System On Output	5VDC @ 20mA	Shipping Size (inch)	101/2Hx22Wx143/4D
External Mute Input	3.3-10VDC	Shipping Weight (kg)	7.5
e e e e e e e e e e e e e e e e e e e		Shipping Weight (lbs)	16.5
		- 1-13	

NuVo reserves the right to change specifications without notice.

Office Toll Free: 866.796.4904 Office Direct: 859.817.7200 Email: sales@nuvotechnologies.com Web: www.nuvotechnologies.com