

2

1

NOTES:





TRANSMISSION PERFORMANCE
 Meet all requirements specified in connecting hardware requirement of:
 ANSI/TIA-568-C.2 Category 6

ELECTRICAL
 Electrical Insulation Resistance : 500MΩ min. @ 100V d.c
 Dielectric Withstanding Voltage : 1000V d.c. or a.c. Peak Contact to Contact @ 60Hz for 1 minute

MECHANICAL
 Insertion / Extraction Life : 750 Cycles Minimum
 IDC Wire Gauge : 22 ~ 24 AWG
 Housing : High-Impact, Flame-Retardant Plastic, UL 94V-0
 Spring Wire : Phosphor Bronze Alloy Plated With 50 micro-inch of Gold
 IDC : Phosphor Bronze Alloy With 100 micro-inch 100% Sn Alloy

B

B



A

A

PROPRIETARY AND CONFIDENTIAL THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF ORN-Q/LEGRAND. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF ORN-Q/LEGRAND IS PROHIBITED. DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE.



P.O. Box 60907
 Middletown, PA 17106-0907
 1-800-321-2343

TITLE: 6 PORT CAT 6 DATA BOARD

SIZE	DWG NO	FILE NAME	CUST REV
A	AC0606	CD-AC0606	1
REVISED DATE	SCALE	SHEET	
15/09/22	NONE	1 OF 1	

ACAD

2

1