

2

1

NOTES:

TRANSMISSION PERFORMANCE

Meet all requirements specified in connecting hardware requirement of:

ANSI/TIA-568-C.2, Category 5e

ELECTRICAL

Electrical Insulation Resistance : 500MΩ min. @ 100V d.c

Dielectric Withstanding Voltage : 1000V d.c. or

a.c. Peak Contact to Contact @ 60Hz for 1 minute

MECHANICAL

Insertion / Extraction Life : 750 Cycles Minimum

IDC Wire Gauge : 22 ~ 24 AWG





Housing : High-Impact, Flame-Retardant Plastic, UL 94V-0

Spring Wire : Phosphor Bronze Alloy Plated With 50 micro-inch of Gold

IDC : Phosphor Bronze Alloy With 100 micro-inch 100% Sn Alloy

B

B



A

A

PROPRIETARY AND CONFIDENTIAL THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF ON-Q/LEGRAND. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF ON-Q/LEGRAND IS PROHIBITED. DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE.



P.O. Box 60907
Middletown, PA 17106-0907
1-800-321-2343

TITLE: COMBO PHONE & 5e DATA BOARD

SIZE	DWG NO	FILE NAME	CUST REV
A	TM0404	CD-TM0404	1
REVISED DATE	SCALE	SHEET	
15/09/22	NONE	1 OF 1	

2

1