

NUVO

In-Wall Dual Passive 8" Subwoofer

Delivering a stand-out bass response, the In-Wall Dual Passive 8" Subwoofer brings a whole new dimension of detailed clarity to movies and music. With a discrete design that allows for space-saving in-wall placement, the NV-SUBIWDUAL8 adds a powerful low-frequency impact to medium and larger home theater or audio installations. Its sealed cabinet is constructed of durable MDF for a distortion-free, superior bass experience. A rectangular magnetic grill is included.



- Discrete wall-mounted passive dual 8" subwoofer ideal for medium and larger sized audio installations
- Installation-friendly sealed cabinet design
- Pair up with optional NV-SUBAMP500-xx amplifier
- Rectangular magnetic grill included
- Up to two dual subwoofers may be used with optional NV-SUBAMP500-xx amplifier
- Lifetime warranty
- Space-saving design

The NV-SUBAMP500 optional matching amplifier offers maximum versatility with rack-mount capability. The pair are designed to integrate with almost any audio system. The NV-SUBAMP500-xx features DSP (digital signal processing) for a variety of listening modes, an easy to navigate front screen for set up and use, signal-sensing power activation (optional setting) to automatically turn on the subwoofer when it detects a signal from the receiver. It will return to standby automatically after approximately 15 minutes of no signal. Unfiltered LFE / RCA stereo inputs let you easily connect the amplifier to most modern receivers. The variable crossover and phase controls allow you to match the Subwoofer output with the main speakers for premium performance and sound. Convenient 12V DC trigger inputs and outputs allow the amplifier to be controlled by external devices or control other external items. An IR input allows for simple external control as well. A three-position EQ menu setting allows the amplifier output to be tailored to any Nuvo in-ceiling or in-wall passive subwoofers. One or two NV-SUBIWDUAL8 subwoofers may be used with one NV-SUBAMP500-xx.



NV-SUBAMP500

Nuvo In-Wall Dual Passive 8" Subwoofer

Material	MDF Enclosure with Aluminum Frame and Steel Grill
Color	Black with White Grill
Unit Size	
(mm)	547.6 x 347.6 x 106.8
(in)	21.6 x 13.7 x 4.2
Unit Weight	
(kg)	10.2
(lbs)	22.49
Shipping	
Package Dimensions (mm)	655 x 465 x 260
Package Dimensions (in)	25.8 x 18.3 x 10.2
Package Shipping Weight (kg)	12.5
Package Shipping Weight (lbs)	27.56
Humidity	70% non-condensing
Interoperability	Use up to two units with NV-SUBAMP500-xx
Mounting	
In-Wall Rectangular Cutout	510mm x 310mm (19.75" x 12")
High Level Input Connector	Gold Plated Spring Loaded Binding Posts
Speaker Size	Dual 8" (200mm) High-Output
Enclosure Type	Sealed
Sensitivity	85dB
Frequency	29-200Hz
Speaker Impedance	8 Ohm
Power Consumption	250W RMS 500W Peak
Regulatory Approvals	RoHS (Restriction of Hazardous Substances Directive 2002/95/EC)



designed to be better™



Legrand, North America

3015 Kustom Drive
Hebron, KY 41048
United States
844.334.8044
www.legrand.us/nuvo