

4

3

626TF4ZRYZXXXMC1

OR-626TF4ZR-YZXXXM

1

03

1

NOTES:

1. ALL CABLE ASSEMBLIES DESCRIBED BY THIS DOCUMENT SHALL BE IN ACCORDANCE WITH PERFORMANCE SPECIFICATION OR-71800020.
2. THE NOTATION "XXX" WITHIN THE PART NUMBER SHALL IDENTIFY THE LENGTH FROM BREAKOUT TO BLUNT END AS SHOWN. THE UNITS OF MEASURE ARE INDICATED BY THE CHARACTER POSITION IMMEDIATELY FOLLOWING THE "XXX" PORTION OF THE PART NUMBER (I.E. M=METERS, F=FEET). THE LENGTH TOLERANCE IS -0.00/+0.12 METERS (-0.0/+4.7 INCHES).
3. EACH CABLE SHALL BE IDENTIFIED WITH A 4 DIGIT MANUFACTURE DATE CODE (WWYY=WEEK YEAR) AND LOCATION CODE (XX).
4. CONNECTOR TYPE SHALL BE IDENTIFIED BY CHARACTER POSITION "Y" IN THE PART NUMBER. CHARACTER POSITION 'Z' INDICATES THE OPPOSITE END OF THE CABLE SHALL BE A BLUNT-END TERMINATION. SEE TABLE 1 FOR THE CONNECTOR TYPE DEFINITION.
5. TERMINATION SHALL BE MADE IN ACCORDANCE WITH TABLE 2 OR 3, AS APPLICABLE.
6. EACH TERMINATED FIBER IN THE BREAKOUT REGION SHALL BE COLOR CODED WITH 900um BUFFER AS SHOWN.

⊠ INDICATES NOTE REFERENCE.








TABLE 1					
CONNECTOR ID	CONNECTOR QTY	CONNECTOR IMAGE	CONNECTOR TYPE	SPECIFICATION	FIGURE
C	6		MTRJ(F)	TIA/EIA-604-12	2
D	6		MTRJ(M)	TIA/EIA-604-12	2
E	12		ST	TIA/EIA-604-2	1
F	12		SC	TIA/EIA-604-3	1
G	12		LC	TIA/EIA-604-10	1
H	12		FC	TIA/EIA-604-4	1

TABLE 2 ⊠		
FIBER #	COLOR	CONNECTOR #
1	BLUE	1
2	ORANGE	2
3	GREEN	3
4	BROWN	4
5	SLATE	5
6	WHITE	6
7	RED	7
8	BLACK	8
9	YELLOW	9
10	VIOLET	10
11	ROSE	11
12	AQUA	12

TABLE 3 ⊠		
FIBER #	COLOR	CONNECTOR #
1	BLUE	1
2	ORANGE	2
3	GREEN	3
4	BROWN	4
5	SLATE	5
6	WHITE	6
7	RED	7
8	BLACK	8
9	YELLOW	9
10	VIOLET	10
11	ROSE	11
12	AQUA	12

3	AR				12 FIBER, DIST, MM, RISER, 50/125, 2/.5GHz-km		
2	6				CONNECTOR 2		
1	12				CONNECTOR 1		
⊠	ITEM	QUAN	PART NUMBER	REV	SUPPLIER/VENDOR	TITLE	DESCRIPTION
<p>*** NOTICE *** THIS DOCUMENT CONTAINS CONFIDENTIAL AND/OR PROPRIETARY INFORMATION INTENDED FOR USE ONLY BY THE INDIVIDUAL(S) SPECIFIED HEREIN AND ONLY FOR THE PURPOSE(S) PROVIDED. NEITHER THIS DOCUMENT, NOR ANY INFORMATION CONTAINED HEREIN, MAY BE COPIED, DISTRIBUTED, DISCLOSED TO ANY THIRD PARTY OR USED IN ANY MANNER OTHER THAN FOR WHICH IT HAS BEEN PROVIDED, WITHOUT THE PRIOR WRITTEN CONSENT OF ORTRONICS, INC.</p>						 NEW LONDON, CT 06320 (860) 445-3800	
DWN. BY: RYNSKI		DATE: 12/30/02		SIZE: CAD FILE		PART NUMBER	
CHK. BY: AM		DATE: 01/17/05		SCALE: NONE		DATE: 01/07/05	
APP. BY: MEM		DATE: 01/17/05		SCALE: NONE		DATE: 01/07/05	
						SHEET: 1 OF 2	

4

3

2

1

4

3

626TF4ZRYZXXMC2

OR-626TF4ZR-YZXXM

2

03

1

D

C

B

A




FIGURE 1
SEE TABLE 2




FIGURE 2
SEE TABLE 3
(MALE MTRJ CONNECTOR SHOWN FOR REF ONLY)

ITEM	QUAN	PART NUMBER	REV	SUPPLIER/VENDOR	TITLE	DESCRIPTION
*** NOTICE *** THIS DOCUMENT CONTAINS CONFIDENTIAL AND/OR PROPRIETARY INFORMATION INTENDED FOR USE ONLY BY THE INDIVIDUAL(S) SPECIFIED HEREIN AND ONLY FOR THE PURPOSE(S) PROVIDED. NEITHER THIS DOCUMENT, NOR ANY INFORMATION CONTAINED HEREIN, MAY BE COPIED, DISTRIBUTED, DISCLOSED TO ANY THIRD PARTY OR USED IN ANY MANNER OTHER THAN FOR WHICH IT HAS BEEN PROVIDED, WITHOUT THE PRIOR WRITTEN CONSENT OF ORTRONICS, INC.				 NEW LONDON, CT 06320 (860) 445-3800	FIBER CORD ASSY, PIGTAIL, 12 FIBER, 50/125, MM, DIST, RISER, 2/.5GHz-km	
DWN. BY:	RYNASKI	DATE:	12/30/02	SIZE:	CAD FILE	PART NUMBER
CHK. BY:	AM	DATE:	01/17/05	B	626TF4ZRYZXXMC2	OR-626TF4ZR-YZXXM
APP. BY:	MEM	DATE:	01/17/05	SCALE:	NONE	DATE
						08/04/06
						SHEET
						2 OF 2

4

3

2

1