


25 PAIR TELCO WITH  
90 DEGREE HOOD  
(SPECIFY GENDER)

25 PAIR TELCO WITH  
90 DEGREE HOOD  
(SPECIFY GENDER)



ALL 25PR CABLES ARE MEASURED FROM BACK OF CONNECTOR TO BACK OF CONNECTOR AS SHOWN

ELECTRICAL CHARACTERISTICS:

CONDUCTOR RESISTANCE: 28.6 Ohms ( MAX.) 1000FT.  
(304.8M) 25 PAIR  
MUTUAL CAPACITANCE: 19 pF/ft  
IMPEDANCE: 100 Ohms ±15%

WIRING: WIRE 50 PINS STRAIGHT THROUGH, PIN 1 TO 1.  
AS SHOWN BELOW

CONSTRUCTION:


CONDUCTORS: 24 AWG (0.0191 TO 0.0201 DIA) SOLID ANNEALED BARE COPPER WITH 0.031" TO 0.033" THK. SEMI-RIDGID PVC INSULATION 1-1/2 TWIST PER FT. STANDARD TELEPHONE COLOR CODING 0.014" TO 0.018" PVC OUTER JACKET, OVERALL DIA: 0.33" TO 0.34" O.D.

GENDERS:


P = MALE  
C = FEMALE  
X = BLUNT

TEST REQUIREMENTS:

ALL ASSEMBLIES TO BE WIRE-MAP CONTINUITY TESTED USING CIRRIS TESTER (OR APPROVED EQUAL)



MALE TELCO CONNECTOR SHOWN



CABLE TYPE:

1GY = 24G PVC GRAY  
1BE = 24G PVC BEIGE  
4 = 24G PLENUM CMP

\*\*\* NOTICE \*\*\*

THIS DOCUMENT CONTAINS CONFIDENTIAL AND/OR PROPRIETARY INFORMATION INTENDED FOR USE ONLY BY THE INDIVIDUAL(S) SPECIFIED HEREIN AND ONLY FOR THE PURPOSE(S) PROVIDED. NEITHER THIS DOCUMENT, NOR ANY INFORMATION CONTAINED HEREIN, MAY BE COPIED, DISTRIBUTED, DISCLOSED TO ANY THIRD PARTY OR USED IN ANY MANNER OTHER THAN FOR WHICH IT HAS BEEN PROVIDED, WITHOUT THE PRIOR WRITTEN CONSENT OF ORTRONICS, INC.



NEW LONDON, CT 06320  
(860) 445-3800

DWN.BY: JIM LUCY	DATE: 01/31/03
CHK.BY: S. LEVESQUE	DATE: 09/15/04
APP.BY: M. MARTICH	DATE: 09/15/04

TITLE

25 PR TELCO ASSEMBLY  
25 PR 24G SOLID PVC

SIZE: A	CAD FILE: 804025XXXXX1XXC	PART NUMBER: OR-804025XXXXX-1XX	REV: 01
SCALE: NONE	DATE: 09/10/04	SHEET: 1 OF 1	