



D

C

B

A

- NOTES: UNLESS OTHERWISE SPECIFIED
1. PERFORMANCE SHALL BE IN ACCORDANCE WITH LEGRAND SPECIFICATION #71800076C.
 2. THE "XM" PORTION OF THE PART NUMBER SHALL IDENTIFY THE OVERALL EXTERNAL PIGTAIL LENGTH OF THE ASSEMBLY. THE UNITS OF MEASURE ARE INDICATED BY THE CHARACTER IMMEDIATELY FOLLOWING THE "X" PORTION OF THE PART NUMBER (I.E., M=METERS, F=FEET, H='XM' +1/2 FOOT, S='X'+1/2 METER). LENGTH TOLERANCE IS $\pm .100$ METERS (± 3.95 IN.).
 3. A LABEL SHOWING THE INSERTION LOSS, BY PORT, IS PROVIDED AFFIXED TO THE CASSETTE.
 4. THE CASSETTE BODY IS METAL, PAINTED MAGNESIUM.
 5. INPUT AND OUTPUT PIGTAILS HAVE LABELS FOR CHANNEL AND INPUT IDENTIFICATION.
 6. EACH SPLITTER ASSEMBLY SHALL BE IDENTIFIED WITH "LEGRAND", A PART NUMBER, A 4 DIGIT MANUFACTURE DATE CODE (WWYY=WEEK YEAR), AND LOCATION CODE(XX).



SILKSCREEN DETAIL
SCALE 1:1
(PIGTAILS REMOVED FOR CLARITY)

OR-M4S1216SA09XM

BASE NUMBER

"A"
(SEE NOTE 2)

PART NUMBER LEGEND

*** NOTICE ***
THIS DOCUMENT CONTAINS CONFIDENTIAL
AND/OR PROPRIETARY INFORMATION INTENDED
FOR USE ONLY BY THE INDIVIDUAL(S) PROVIDED.
NEITHER THIS DOCUMENT, NOR ANY
INFORMATION CONTAINED HEREIN, MAY BE
COPIED, DISTRIBUTED, DISCLOSED TO ANY THIRD
PARTY OR USED IN ANY MANNER OTHER THAN
FOR WHICH IT HAS BEEN PROVIDED, WITHOUT
THE PRIOR WRITTEN CONSENT OF LEGRAND, INC.
MANUFACTURING RELEASE, PRODUCT
SPECIFICATIONS AND STANDARDS ARE SUBJECT
TO CHANGE WITHOUT NOTICE.

legrand®

WWW.LEGRAND.US

TITLE

SPLITTER, DUAL 1 X 16, WITH PIGTAILS, M4
FORM FACTOR

	NAME	DATE	SIZE	CAD FILE	DWG NO	REV
DWN	RYNASKI	11/8/2012	B	M4S1216SA09XMC	M4S1216SA09XM	01
CHK	A. RICHARD	11/13/2012	SCALE	1:2	WEIGHT	SHEET
APPR	A. MURANO	11/13/2012				