


125 EUGENE O'NEILL DRIVE NEW LONDON, CT 06320

TEL: 860-445-3800 FAX: 860-405-2990 TITLE: OR-71601774


CLARITY ANGLED & CURVED PANELS,


CAT6A, WITH 6-PORT MODULES

PORTS	JACK	DENSITY	WIRING	SIZE (A)	ANGLED PN#	CURVED PN#	
				, ,	(CAT6A)	(CAT6A)	
24 PORT	8 POS/RJ45	HD	T568 B OR A	1.75 X 19	PHA6AU24	PHC6AU24	
48 PORT	8 POS/RJ45	HD	T568 B OR A	3.50 X 19	PHA6AU48	PHC6AU48	




FRONT VIEW 24 PORT





REAR VIEW 24 PORT




COLOR 8 CODE RJ	68A POS. JACK 45 RING	STATION CABLE COLOR CODE T568B	T568B 8 POS. RJ45 WIRING	JACK
WHITE/BLUE BLUE/WHITE	5 4	WHITE/BLUE BLUE/WHITE	5 4	
WHITE/ORANGE ORANGE/WHITE	3	WHITE/ORAN ORANGE/WHI		
WHITE/GREEN	1	WHITE/GREEN	١ 3	
GREEN/WHITE WHITE/BROWN	2 7	GREEN/WHITE	N 7	
BROWN/WHITE	8	BROWN/WHIT	E 8	

RJ**4**5 PIN #'s

NOTES:

 PANEL IS SUPPLIED WITH T568B LABEL IN PLACE. FOR T568A WIRING, ATTACH FOUR SUPPLIED T568A WIRING LABELS.
 MAINTAIN PAIR TWIST UP TO POINT

 MAINTAIN PAIR TWIST UP TO POIN' OF TERMINATION FOR MAXIMUM DATA PERFORMANCE.



OR-60300005 (TOOL) OR-60300006 (BLADE)

HITE/BROWN 7 DATA PERFO ROWN/WHITE 8	ORMANCE.
---	----------

INSTRUCTION SHEET #	REV.	ECN#	SHEET	DWN. BY:	DATE	CHK. BY:	DATE	APP. BY:	DATE
OR-71601774	00		1 of 2	K. CUPPLES	04/19/11	C.A.C./G.L.	04/19/11	W. DIETZ	04/20/11




125 EUGENE O'NEILL DRIVE NEW LONDON, CT 06320


TEL: 860-445-3800 FAX: 860-405-2990 TITLE: OR-71601774

CLARITY ANGLED & CURVED PANELS,

CAT6A, WITH 6-PORT MODULES




ANGLED PATCH PANEL




110 PATCH PANEL INSTRUCTIONS:


- 1. PLACE WIRE MANAGEMENT BRACKET OVER THREADED STUDS IN 'B' POSITION.
- APPLY 2 WING NUTS. (TIGHTEN AS REQUIRED)
- AFTER CABLE TERMINATION IS COMPLETED AS RECOMMENDED BELOW, ADJUST BRACKET TO 'A' POSITION.

NOTE: GRAY STUFFER CAPS MUST BE INSTALLED FOR CAT6A PERFORMANCE.




FOR OPTIMUM CABLE MANAGEMENT, THE CABLES SHOULD BE ROUTED AND TERMINATED WORKING FROM THE OUTSIDE EDGES OF THE PATCH PANEL TO THE CENTER. NOTE: THE CABLES SHOULD BE ROUTED FROM BOTH SIDES OF THE RELAY RACK RATHER THAN FROM ONE SIDE ONLY.





THE MINIMUM CABLE BEND RADIUS IS 4 TIMES THE OUTSIDE CABLE DIAMETER. HOOK & LOOP WRAPS SHOULD BE USED TO ATTACH THE CABLE TO THE WIRE MANAGEMENT BRACKET.



- 1) REMOVE NEAREST WING NUT & WIRE MANAGER FROM STUD.
- 2) REMOVE WIRE MANAGER SLIDE GUIDE FROM STUD.
- 3) PUSH OUT BEZEL LOCKING TABS WITH SLOT PROVIDED.
- 4) WITHDRAW MODULE TO THE REAR OF THE PANEL FROM BEZEL LOCKING TABS.
- 5) REASSEMBLE IN REVERSE ORDER

INSTRUCTION SHEET #	REV.	ECN#	SHEET	DWN. BY:	DATE	CHK. BY:	DATE	APP. BY:	DATE
OR-71601774	00		2 OF 2	K. CUPPLES	04/19/11	C.A.C./G.L.	04/19/11	W. DIETZ	04/20/11