

iq.ul.com

Component - Plastics [\[guide info\]](#)

E162823

**FORMOSA CHEMICALS & FIBRE CORP PLASTICS DIV**

201 TUNG HWA N RD, TAIPEI 105 TW

**AC310(+)**

Polycarbonate/Acrylonitrile Butadiene Styrene (PC/ABS), "TAIRILOY", furnished as pellets

Color	Min Thk (mm)	Flame Class	HWI	HAI	RTI Elec	RTI Imp	RTI Str
ALL	1.2	V-0	3	0	60	60	60
	1.5	V-0	3	0	90	85	90
	2.3	V-0, 5VB	2	0	90	85	90
	3.0	V-0, 5VA	-	-	90	85	90

Comparative Tracking Index (CTI): 0

Dielectric Strength (kV/mm): -

High-Voltage Arc Tracking Rate (HVTR): 3

Dimensional Stability (%): -

Inclined Plane Tracking (IPT): -

Volume Resistivity (10<sup>x</sup> ohm-cm): -High Volt, Low Current Arc Resis  
(D495): 7

(+) - Replace by one digital 0-9 or one alphabet A-Z, unconcerned with formula or constituent changed

ANSI/UL 94 small-scale test data does not pertain to building materials, furnishings and related contents. ANSI/UL 94 small-scale test data is intended solely for determining the flammability of plastic materials used in the components and parts of end-product devices and appliances, where the acceptability of the combination is determined by UL.

Report Date: 1999-10-14

Last Revised: 2015-07-30

© 2015 UL LLC

**IEC and ISO Test Methods**

Test Name	Test Method	Units	Thk (mm)	Value
Flammability	IEC 60695-11-10, IEC 60695-11-20	Class (color)	1.2	V-0 (ALL)
			1.5	V-0 (ALL)
			2.3	V-0, 5VB (ALL)
			3.0	V-0, 5VA (ALL)
Glow-Wire Flammability (GWFI)	IEC 60695-2-12	C	-	-
Glow-Wire Ignition (GWIT)	IEC 60695-2-13	C	-	-
IEC Comparative Tracking Index	IEC 60112	Volts (Max)	-	-
IEC Ball Pressure	IEC 60695-10-2	C	3.0	75
ISO Heat Deflection (1.80 MPa)	ISO 75-2	C	-	-
ISO Tensile Strength	ISO 527-2	MPa	-	-
ISO Flexural Strength	ISO 178	MPa	-	-
ISO Tensile Impact	ISO 8256	kJ/m <sup>2</sup>	-	-
ISO Izod Impact	ISO 180	kJ/m <sup>2</sup>	-	-
ISO Charpy Impact	ISO 179-2	kJ/m <sup>2</sup>	-	-