

NOTES: UNLESS OTHERWISE SPECIFIED

- PERFORMANCE SHALL BE IN ACCORDANCE WITH LEGRAND SPECIFICATION #71800076C.
- THE "XM" PORTION OF THE PART NUMBER SHALL IDENTIFY THE OVERALL EXTERNAL PIGTAIL LENGTH OF THE ASSEMBLY. THE UNITS OF MEASURE ARE INDICATED BY THE CHARACTER IMMEDIATELY FOLLOWING THE "X" PORTION OF THE PART NUMBER (I.E., M=METERS, F=FEET, H='XM' +1/2 FOOT, S='X'+1/2 METER). LENGTH TOLERANCE IS  $\pm .100$  METERS ( $\pm 3.95$  IN.).
- A LABEL SHOWING THE INSERTION LOSS, BY PORT, IS PROVIDED AFFIXED TO THE CASSETTE.
- THE CASSETTE BODY IS METAL, PAINTED MAGNESIUM.
- INPUT AND OUTPUT PIGTAILS HAVE LABELS FOR CHANNEL AND INPUT IDENTIFICATION.
- EACH SPLITTER ASSEMBLY SHALL BE IDENTIFIED WITH "LEGRAND", A PART NUMBER, A 4 DIGIT MANUFACTURE DATE CODE (WWYY=WEEK YEAR), AND LOCATION CODE (XX).

D

C

B




A

D

C

B

A



OR-M4S2132SA09XM  
 BASE NUMBER "A" (SEE NOTE 2)

PART NUMBER LEGEND

\*\*\* NOTICE \*\*\*  
 THIS DOCUMENT CONTAINS CONFIDENTIAL AND/OR PROPRIETARY INFORMATION INTENDED FOR USE ONLY BY THE INDIVIDUAL(S) PROVIDED. NEITHER THIS DOCUMENT, NOR ANY INFORMATION CONTAINED HEREIN, MAY BE COPIED, DISTRIBUTED, DISCLOSED TO ANY THIRD PARTY OR USED IN ANY MANNER OTHER THAN FOR WHICH IT HAS BEEN PROVIDED, WITHOUT THE PRIOR WRITTEN CONSENT OF LEGRAND, INC. MANUFACTURING RELEASE, PRODUCT SPECIFICATIONS AND STANDARDS ARE SUBJECT TO CHANGE WITHOUT NOTICE.

	NAME	DATE
DWN	RYNASKI	11/8/12
CHK	A. RICHARD	11/14/12
APPR	A. MURANO	11/14/12

<b>legrand</b> ®		WWW.LEGRAND.US	
TITLE SPLITTER, 2 X 32, SC(APC), WITH PIGTAILS, M4 FORM FACTOR			
SIZE B	CAD FILE M4S2132SA09XMC	DWG NO M4S2132SA09XM	REV 01
SCALE 1:2	WEIGHT	SHEET 1 OF 1	

4

3

2

1