

Sarlink® TPV 4165

Teknor Apex Company - Thermoplastic Vulcanizate

Monday, February 20, 2017

General Information

Product Description

SARLINK® TPV 4100 series are engineered materials designed primarily for demanding automotive and industrial applications. Available in both black and natural, SARLINK® 4165 is a low density, medium hardness thermoplastic vulcanizate that exhibits excellent compression set, flex fatigue, high and low temperature performance. The material can be processed by injection molding, blow molding and extrusion for applications such as seals, gaskets, chemical resistant hose and tube, boots and bellows.

General

Material Status	• Commercial: Active		
Availability	• Asia Pacific • Europe	• Latin America • North America	
Features	• Chemical Resistant • Excellent Elastic Recovery • Fatigue Resistant • Good Adhesion • Good Flexibility	• Good Moldability • Good Processability • Good Surface Finish • High Melt Stability • Low Density	• Medium Hardness • Medium Heat Resistance • Resilient
Uses	• Appliance Components • Automotive Applications • Automotive Exterior Parts • Automotive Interior Parts • Automotive Under the Hood • Blow Molding Applications	• Gaskets • Grommets • Hose • Industrial Applications • O-rings • Pipe Seals	• Plugs • Rubber Replacement • Seals • Tubing • White Goods & Small Appliances
Agency Ratings	• UL QMFZ2	• UL QMFZ8	
RoHS Compliance	• RoHS Compliant		
Automotive Specifications	• BMW Unspecified Color: Black • CHRYSLER MS-AR-100 BGN Color: Black • CHRYSLER MS-AR-100 BGN Color: Natural • FORD WSD-M2D378-A6 Color: Black	• FORD WSD-M2D379-A1 Color: Black • FORD WSD-M2D379-A1 Color: Natural • GM GMP/E/P.002 Color: Black • GM GMP/E/P.002 Color: Natural	• GM GMW15813 Type 5 Color: Black • GM GMW15813 Type 5 Color: Natural • GM QK 3521 Type 1 Color: Black • GM QK 3521 Type 1 Color: Natural
Appearance	• Black	• Natural Color	• Opaque
Forms	• Pellets		
Processing Method	• Blow Molding	• Extrusion	• Injection Molding

ASTM & ISO Properties ¹

Physical	Nominal Value	Unit	Test Method
Specific Gravity	0.960		ASTM D792
Density	0.960	g/cm ³	ISO 1183
Elastomers	Nominal Value	Unit	Test Method
Tensile Stress			
Across Flow : 100% Strain	363	psi	ASTM D412
Across Flow : 100% Strain	363	psi	ISO 37
Flow : 100% Strain	609	psi	ISO 37
Flow : 100% Strain	609	psi	ASTM D412
Tensile Stress			
Across Flow : Break	986	psi	ASTM D412
Across Flow : Break	986	psi	ISO 37
Flow : Break	841	psi	ASTM D412
Flow : Break	841	psi	ISO 37

Revision Date: 8/4/2016

The information and recommendations contained in this bulletin are, to the best of our knowledge, accurate and reliable but no guarantee of their accuracy is made. All products are sold upon condition that purchasers shall make their own tests to determine the suitability of such products for their particular purposes and uses and purchasers assume all risks and liability for the results of use of the products, including use in accordance with seller's recommendations. Nothing in this bulletin constitutes permission or a recommendation to practice or use any invention covered by any patent owned by this company or by others. There is no warranty of merchantability and there are no other warranties for the products described.

Sarlink® TPV 4165

Teknor Apex Company - Thermoplastic Vulcanizate

Elastomers	Nominal Value	Unit	Test Method
Tensile Elongation			
Across Flow : Break	570	%	ASTM D412
Across Flow : Break	570	%	ISO 37
Flow : Break	280	%	ASTM D412
Flow : Break	280	%	ISO 37
Tear Strength - Across Flow			
--	170	lbf/in	ASTM D624
-- ²	170	lbf/in	ISO 34-1
Compression Set			
73°F, 22 hr	17	%	ASTM D395
73°F, 22 hr	17	%	ISO 815
158°F, 22 hr	27	%	ASTM D395
158°F, 22 hr	27	%	ISO 815
257°F, 70 hr	40	%	ASTM D395
257°F, 70 hr	40	%	ISO 815
Hardness	Nominal Value	Unit	Test Method
Shore Hardness			
Shore A, 5 sec, Extruded	63		ASTM D2240
Shore A, 5 sec, Extruded	63		ISO 868
Shore A, 5 sec, Injection Molded	65		ASTM D2240
Shore A, 5 sec, Injection Molded	65		ISO 868
Thermal	Nominal Value	Unit	Test Method
Brittleness Temperature	-85.0	°F	ASTM D746
RTI Elec	212	°F	UL 746
RTI Imp	149	°F	UL 746
RTI Str	212	°F	UL 746
Aging	Nominal Value	Unit	Test Method
Change in Tensile Strength in Air - Across Flow			
275°F, 1000 hr	-9.0	%	ISO 188
275°F, 1000 hr	-9.0	%	ASTM D573
302°F, 168 hr	-11	%	ASTM D573
302°F, 168 hr	-11	%	ISO 188
100% Strain 302°F, 168 hr	0.0	%	ISO 188
100% Strain 302°F, 168 hr	0.0	%	ASTM D573
100% Strain 302°F, 1000 hr	4.0	%	ISO 188
100% Strain 302°F, 1000 hr	4.0	%	ASTM D573
Change in Tensile Strain at Break in Air - Across Flow			
275°F, 1000 hr	-8.0	%	ASTM D573
275°F, 1000 hr	-8.0	%	ISO 188
302°F, 168 hr	-11	%	ISO 188
302°F, 168 hr	-11	%	ASTM D573
Change in Shore Hardness in Air			
Shore A, 275°F, 1000 hr	2.0		ASTM D573
Shore A, 275°F, 1000 hr	2.0		ISO 188
Shore A, 302°F, 168 hr	2.0		ISO 188
Shore A, 302°F, 168 hr	2.0		ASTM D573
Change in Volume			
257°F, 70 hr, in IRM 903 Oil	83	%	ASTM D471
257°F, 70 hr, in IRM 903 Oil	83	%	ISO 1817

Revision Date: 8/4/2016

The information and recommendations contained in this bulletin are, to the best of our knowledge, accurate and reliable but no guarantee of their accuracy is made. All products are sold upon condition that purchasers shall make their own tests to determine the suitability of such products for their particular purposes and uses and purchasers assume all risks and liability for the results of use of the products, including use in accordance with seller's recommendations. Nothing in this bulletin constitutes permission or a recommendation to practice or use any invention covered by any patent owned by this company or by others. There is no warranty of merchantability and there are no other warranties for the products described.

Sarlink® TPV 4165

Teknor Apex Company - Thermoplastic Vulcanizate

Electrical	Nominal Value	Unit	Test Method
Volume Resistivity	1.0E+16	ohms·cm	ASTM D257
Flammability	Nominal Value	Unit	Test Method
Flame Rating (0.04 in, All Colors)	HB		UL 94
Additional Information	Nominal Value	Unit	Test Method
Apparent Shear Viscosity - Capillary, @ 206/s			
392°F	340	Pa·s	ASTM D3835
392°F	340	Pa·s	ISO 11443

Legal Statement

The information and recommendations contained in this bulletin are, to the best of our knowledge, accurate and reliable but no guarantee of their accuracy is made. All products are sold upon condition that purchasers shall make their own tests to determine the suitability of such products for their particular purposes and uses and purchaser assumes all risks and liability for the results of use of the products, including use in accordance with seller's recommendations. Nothing in this bulletin constitutes permission or a recommendation to practice or use any invention covered by any patent owned by this company or others. There is no warranty of merchantability and there are no other warranties for the products described. For detailed Product Stewardship information, please contact us. Any product of Teknor Apex, including product names, shall not be used or tested in medical or food contact applications without the prior written acknowledgement of Teknor Apex as to the intended use. Please note that some products may not be available in one or more countries.

Processing Information

Injection	Nominal Value	Unit
Drying Temperature	180	°F
Drying Time	3.0	hr
Rear Temperature	356 to 419	°F
Middle Temperature	356 to 419	°F
Front Temperature	356 to 419	°F
Nozzle Temperature	369 to 428	°F
Processing (Melt) Temp	365 to 428	°F
Mold Temperature	50 to 131	°F
Back Pressure	14.5 to 145	psi
Screw Speed	100 to 200	rpm
Extrusion	Nominal Value	Unit
Drying Temperature	180	°F
Drying Time	3.0	hr
Cylinder Zone 1 Temp.	356 to 392	°F
Cylinder Zone 2 Temp.	356 to 401	°F
Cylinder Zone 3 Temp.	369 to 410	°F
Cylinder Zone 4 Temp.	369 to 410	°F
Melt Temperature	383 to 419	°F
Die Temperature	383 to 419	°F
Take-Off Roll	68 to 122	°F

Extrusion Notes

Screen Pack: 20 to 60 mesh
Screw: general purpose
Compression Ratio: 3:1

Notes

¹ Typical properties: these are not to be construed as specifications.

² Method Ba, Angle (Unnicked)

Revision Date: 8/4/2016

The information and recommendations contained in this bulletin are, to the best of our knowledge, accurate and reliable but no guarantee of their accuracy is made. All products are sold upon condition that purchasers shall make their own tests to determine the suitability of such products for their particular purposes and uses and purchasers assume all risks and liability for the results of use of the products, including use in accordance with seller's recommendations. Nothing in this bulletin constitutes permission or a recommendation to practice or use any invention covered by any patent owned by this company or by others. There is no warranty of merchantability and there are no other warranties for the products described.

Sarlink® TPV 4165

Teknor Apex Company - Thermoplastic Vulcanizate

Teknor Apex Company Corporate Headquarters

*In U.S. for Vinyls, TPEs, Colorants,
Engineered Thermoplastics (Chem Polymer)*
505 Central Avenue
Pawtucket, Rhode Island 02861 U.S.

Phone: 401-725-8000
Fax: 401-725-8095
Toll Free (U.S. only) 800-556-3864

www.teknorapex.com
info@teknorapex.com

Teknor Apex U.K. Ltd.

Tat Bank Road
Oldbury, West Midlands B69 4NH England

Phone: (44) 121-665-2100
Fax: (44) 121-544-5530

www.teknorapex.com
etpsales@teknorapex.co.uk

Teknor Apex (Suzhou) Advanced Polymer Compounds Co. Pte. Ltd.

No. 78 Ping Sheng Road
Suzhou Industrial Park
Jiangsu, China 215126

Phone: (86) 512-6287-1550
Fax: (86) 512-6288-8371

www.teknorapex.com
infotaap@teknorapex.com

Teknor Apex Asia Pacific PTE. LTD.

41 Shipyard Road
Singapore 628134

Phone: (65) 6265-2544
Fax: (65) 6265-1821

www.teknorapex.com
infotaap@teknorapex.com

Revision Date: 8/4/2016

The information and recommendations contained in this bulletin are, to the best of our knowledge, accurate and reliable but no guarantee of their accuracy is made. All products are sold upon condition that purchasers shall make their own tests to determine the suitability of such products for their particular purposes and uses and purchasers assume all risks and liability for the results of use of the products, including use in accordance with seller's recommendations. Nothing in this bulletin constitutes permission or a recommendation to practice or use any invention covered by any patent owned by this company or by others. There is no warranty of merchantability and there are no other warranties for the products described.