

WATTSTOPPER®

Toggle Slide CFL/LED & Incandescent/
Halogen SSL7A Two-Wire Dimmer
250W CFL/LED & 300W Incandescent/Halogen

Energy-saving dimming for CFL, LED, Incandescent and Halogen loads.



TSDSSL7APW

TSDSSL7AP*

Replace your standard switch with the new Toggle Slide Dimmer by Legrand. The new Toggle Slide Dimmer offering has been optimized for today's complicated dimmable bulb market. Different bulbs require different dimming solutions and Legrand has you covered for all your lighting needs. The ergonomic slider was designed with the end user in mind, making it easier to adjust in the dark or on the run.

Compatible with CFL/LED and Incandescent/Halogen dimmable bulbs (with the exception of 0-10V LED drivers), these dimmers feature constant memory that returns lights to the previous level after a power failure for automatic control and convenience.

*Denotes color suffix


Features & Benefits

No neutral wire required

New aesthetically pleasing ergonomic design allows for easier operation

Constant memory returns lights to previous levels after a power failure

Screw-pressure-plate backwire terminals save time, space and money



TSDSSL7APW

Calibration button allows users to adjust minimum and maximum trim levels for a wide range of CFL and LED bulbs

Interchangeable face plates available in seven colors (TSDKIT*; sold separately)

Convenient operation – combines ON/OFF toggle switch with separate slider for dimming control

- Preset, Single Pole and 3-Way operation.
- Compatible with CFL/LED and Incandescent/Halogen dimmable bulbs (with the exception of 0-10V LED drivers).
- Lifetime warranty.



3rd Party Compliance

cULus listed, UL1472, CSA LISTED

Technical Information
Performance
Electrical


Supply Voltage	120VAC
Ratings	250W CFL/LED; 300W Incandescent/Halogen
Frequency	60Hz
Installation	Single Pole or 3-Way

Environmental

Application	Indoor Use Only
-------------	-----------------

Mechanical

Enclosure Material	Polycarbonate
--------------------	---------------


TSDSSL7APW
Warranty

Lifetime

Ordering Information
CFL/LED Incandescent/Halogen SSL7A Two-Wire Dimmers

Catalog Number	Description	Color	Voltage	Rating
TSDSSL7APTC	Preset, Single Pole and 3-Way	Three interchangeable Face Colors: Ivory, White, Light Almond	120VAC 60Hz	300W Inc/Halogen 250W CFL/LED
TSDSSL7APW	Preset, Single Pole and 3-Way	Face Color: White	120VAC 60Hz	300W Inc/Halogen 250W CFL/LED
TSDSSL7APLA	Preset, Single Pole and 3-Way	Face Color: Light Almond	120VAC 60Hz	300W Inc/Halogen 250W CFL/LED
TSDSSL7API	Preset, Single Pole and 3-Way	Face Color: Ivory	120VAC 60Hz	300W Inc/Halogen 250W CFL/LED
TSDSSL7AP	Preset, Single Pole and 3-Way	Face Color: Brown	120VAC 60Hz	300W Inc/Halogen 250W CFL/LED
TSDSSL7APBK	Preset, Single Pole and 3-Way	Face Color: Black	120VAC 60Hz	300W Inc/Halogen 250W CFL/LED
TSDSSL7APRED	Preset, Single Pole and 3-Way	Face Color: Red	120VAC 60Hz	300W Inc/Halogen 250W CFL/LED
TSDSSL7APGRY	Preset, Single Pole and 3-Way	Face Color: Gray	120VAC 60Hz	300W Inc/Halogen 250W CFL/LED
TSDKIT		Brown		
TSDKITBK		Black		
TSDKITGRY		Gray		
TSDKITI	Interchangeable Faces	Ivory		
TSDKITLA		Light Almond		
TSDKITW		White		
TSDKITRED		Red		

Vertical Markets

- Office
- Residential
- Multiple Dwelling
- Hospitality/Lodging

Available in the radiant® collection

- GFCI Receptacles
- Tamper-Resistant and Standard Duplex Receptacles
- Paddle Switches
- Fan Controls
- Sensors
- Timers
- Home Automation Controls
- USB Charging Devices
- Night Lights
- Screwless Wall Plates

 The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act compliant. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.



Legrand, North America
60 Woodlawn Street
West Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us
905.738.9195
www.legrand.ca

