



PASS & SEYMOUR®

PlugTail® Hospital Grade Tamper-Resistant Weather-Resistant Self-Test GFCIs 15 & 20A, 125VAC



PlugTail® GFCIs – The fastest, most consistent and reliable wiring devices – ever.

PT1597HGTRWR* (W, I, LA, BK, GRY, RED)
PT2097HGTRWR* (W, I, LA, BK, GRY, RED)

The new Pass & Seymour® PlugTail Hospital Grade Tamper-Resistant Weather-Resistant Self-Test GFCI receptacle with SafeLock® Protection conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the indicator light flashes to signal that the GFCI should be replaced. It also has our proven SafeLock Protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected.

For non-Hospital Grade PlugTail Self-Test GFCIs, refer to SF1104R4.

Features & Benefits

Patented SafeLock® Protection – if critical components are damaged and ground fault protection is lost, power to the receptacle is disconnected

Galvanized steel mounting strap

The indicator light flashes if the device fails the self-test, signalling that the GFCI should be replaced

The most durable GFCI available. Exceeds UL943 voltage surge requirements.

Tamper-resistant automatic shutter system prevents young children from inserting common household objects

UV-resistant nylon construction for superior strength and durability

Captive zinc-plated steel mounting screws make for easier installation

Meets Federal Specification requirements and 2015 UL requirements

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections to PlugTail Connector


GFCI works with the existing three-wire PlugTail connectors creating a non-feed thru application for facility owners. At rough-in, just install the same right-angle connector for GFCI and receptacle openings.

Large crimped and welded brass contacts snugly terminate on device blade terminals. Audible snapping latch assures connection, allows release

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger-safe housing

No exposed terminals create a finger-safe application before, during, and after installation

Auto-ground clip assures a positive ground to metal box



PT1597HGTRWRLA

3rd Party Compliance



cULus Listed File Number E42190 and E140596, Standard UL498 Attachment Plugs and Receptacles, UL943 GFCIs. Federal Specification WC596. Standard CSA C22.2 No. 42 General Use Receptacles, CSA C22.2 No. 144 GFCIs. Conforms to NEMA WD-1 and WD-6.

Technical Information
Performance
Electrical

Dielectric Voltage	Withstands 1500V minimum
Trip Level	4 to 6 mA
Trip Time	.025 Second Nominal
Frequency	60 Hz
Maximum Working Voltage	125VAC
Voltage Range	102-132VAC

Mechanical

PlugTail Connector Identification	#12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only
Product Identification	Ratings are a permanent part of the device

Environmental

Flammability	UL94 V2
Operating Temperature	-35°C to +66°C
Maximum Humidity	95%

PlugTail® Hospital Grade TR WR GFCI Receptacle Materials



Face	UV-Resistant Nylon
Body	Nylon
Contacts	.03" Brass (.8)
Mounting Straps	Galvanized Steel
Mounting Screws	Zinc-Plated Steel with Black Chromate
Test/Reset Buttons	UV-Resistant Nylon
Tamper-Resistant Shutter	Thermoplastic

PlugTail® Connector Materials

Housing	Polycarbonate
Contacts	.030 Brass

Warranty

1 Year




**Dimensions for
15 & 20 Amp**

PTRA6STR

Ordering Information
PlugTail Hospital Grade Tamper-Resistant Weather-Resistant Self-Test GFCI Receptacles

Catalog Number	Description	Rating		Color	NEMA Configuration No.
		A	V		
PT1597HGTRWRW	PlugTail Hospital Grade Tamper-Resistant Weather-Resistant Self-Test GFCIs	15A	125V	White	5-15R
PT1597HGTRWRI		15A	125V	Ivory	5-15R
PT1597HGTRWRLA		15A	125V	Light Almond	5-15R
PT1597HGTRWRBK		15A	125V	Black	5-15R
PT1597HGTRWRGRY		15A	125V	Gray	5-15R
PT1597HGTRWRRED		15A	125V	Red	5-15R
PT2097HGTRWRW	PlugTail Hospital Grade Tamper-Resistant Weather-Resistant Self-Test GFCIs	20A	125V	White	5-20R
PT2097HGTRWRI		20A	125V	Ivory	5-20R
PT2097HGTRWRLA		20A	125V	Light Almond	5-20R
PT2097HGTRWRBK		20A	125V	Black	5-20R
PT2097HGTRWRGRY		20A	125V	Gray	5-20R
PT2097HGTRWRRED		20A	125V	Red	5-20R

PlugTail Connectors — Right Angle

Catalog Number	Wire Type	Wire Length
PTRA6STR	Stranded	6"
PTRA6SOL	Solid	6"



**NEMA
5-15R**

**NEMA
5-20R**

Vertical Markets

- Industrial
- Retail
- Healthcare
- Office
- Education
- Hospitality/Lodging
- Institutional
- Multiple Dwelling

Also available

- Hospital Grade Devices
- SPD & Isolated Ground Devices
- Ground Continuity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- Turnlok® Locking Devices
- Waterproof Boxes & Covers
- IEC 309 Industrial Products
- Flexcor® Wire Mesh Grips
- Bulk Solutions

 The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act compliant. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.



Legrand, North America
60 Woodlawn Street
West Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us
905.738.9195
www.legrand.ca

