



## Enable instant notification of unsafe conditions.

14W47GCM, 15W47GCM, 14W33GCM, 15W33GCM, 26W47GCM, 27W47GCM

Built-in, UL-Listed testing monitors ground continuity upstream all the way to the panel. Continuous monitoring of ground continuity and power status, in addition to LED indication information on yellow labels, aids in troubleshooting.

Rated watertight for 1,500 psi high-pressure hosedown, these plugs and connectors feature multiple seals to ensure protection against the environment. Constructed of a sturdy rubber body, which makes them impact- and chemical-resistant, they have nickel-plated blades and contacts for superior corrosion resistance.

And thanks to quick-drive assembly screws and backed-out, ready-to-wire terminal screws, these P&S Watertight GCM Plugs and Connectors offer a fast and easy installation — saving time and money in any application.

## Features & Benefits

**Dual, bright LED indicators** with 360° visibility. Blue LEDs indicate proper ground continuity and power status. Red LEDs indicate ground continuity loss or reversed polarity. No LED indicates open hot, open neutral, or hot to ground cross.

**Integral indication of ground continuity and power status.** Continuous monitoring enhances personnel safety and adds convenience.

**Thermoplastic elastomer body construction** stands up to impacts, oils, chemicals, heat, and weather.

**Large ribs on body** for a superior grip when mating.

**Quick-drive assembly screws** allow for fast installation, saving time and money.



**NEMA 4, 4X, 6, 6P Watertight. IP65, 66, 67.**  
Rated watertight for 1,500 psi high-pressure hose-down.

**Terminal screws backed-out, ready-to-wire,** saving time and money.

**Multipoint sealing system between plug and connector** ensures protection from water and contaminants.



**Valox compression-type cord grip** provides watertight seal and great pull out strength.

**Nickel-plated blades and contacts** for long-lasting, superior corrosion resistance.

**15W47 and 14W47**

## Compliance



UL Listed, Standard UL498 (Plug/Connector).

CSA Certified, Standard CSA C22.2 No. 42. Conforms to NEMA WD-1, WD-6 and ANSI standards.

## Technical Information

### Performance

#### Electrical

Dielectric Withstand Voltage	
Connectors:	2000V AC if rated 300V or less
	3000V AC if rated above 300V
Plugs:	2500V AC if rated 300V or less
	3500V AC if rated above 300V
Maximum Working Voltage	As marked
Current Interrupting	Rated for current interruption per UL498
Temperature Rise	30°C maximum per UL498 at rated current

#### Mechanical


Cord & Terminal Accommodations:	
Plugs & Connectors	
15A & 20A Straight Blade and 15A locking	Type S, SO, ST, SJ, SJO, SJT, 18/3 to 12/3, .300 min. to .625 in. max [7.6 to 15.9mm] dia.
20A & 30A 3-wire locking	12/3 SJ, 14/3 S to 10/3 S, (.475" to .720") [12.1mm to 19.2mm]
20A 4-wire locking	14/4 S to 10/4 S, (.560" to .775") [14.2mm to 19.9mm]
30A 4-wire locking	12/4 S to 8/4 S, 6/4 MSHA (.640" to .930") [16.3mm to 23.6mm]
All 15A & 20A straight blade	18 AWG to 12 AWG
20A locking & 30A 3-wire	14 AWG to 10 AWG
30A 4-wire	12 AWG to 6 AWG

#### Environmental


Moisture Resistance	NEMA 4, 4X, 12, 6, 6P (Plug & Connector only)
Flammability	UL94V0 (boxes & wiring device interiors)
Operating Temperature	-40°C (without impact) to +60°C continuous
UV resistance	All exposed materials are UV stabilized

#### Materials

Body/Contact Carrier	PBT Thermoplastic, Yellow
Terminal Retainer	Polycarbonate, Clear
Housing	Thermoplastic Elastomer, Yellow/Transparent
Housing Insert	Polypropylene, Natural
Strain Relief Nut	PBT Thermoplastic, Black
Grommet	Thermoplastic Elastomer, Various Colors
Ferrule	Polypropylene, Natural
Blades/Contacts	Brass, Nickel
Terminal Screws	Steel, Chromate
Terminal Screw Size	#8-32
Body Holding Screws	Stainless Steel
Drive Screws	Steel, Chromate



**14W47GCM**



**15W47GCM**

#### Straight Blade

(Inch)	A	B
<b>Watertight Plug</b>		
15A	2.62"	1.85"
20A	2.62"	1.85"

#### Watertight Connector

15A	4.03"	1.85"
20A	4.03"	1.85"

#### Turnlok®

(Inch)	A	B
<b>Watertight Plug</b>		
20A	2.62"	1.85"
<b>Watertight Connector</b>		
20A	4.03"	1.85"

### Warranty

1 Year

## Ordering Information

### Straight Blade & Turnlok® Watertight GCM Plugs & Connectors

Catalog Number	Description	Rating		NEMA Config. No.	Color
		A	VAC		
<b>14W47GCM</b>	Straight Blade IP67 Ground Continuity Monitoring Plug	15	125V	5-15P	Yellow
<b>15W47GCM</b>	Straight Blade IP67 Ground Continuity Monitoring Connector	15A	125V	5-15R	Yellow
<b>14W33GCM</b>	Straight Blade IP67 Ground Continuity Monitoring Plug	20A	125V	5-20P	Yellow
<b>15W33GCM</b>	Straight Blade IP67 Ground Continuity Monitoring Connector	20A	125V	5-20R	Yellow
<b>26W47GCM*</b>	Turnlok® Watertight Ground Continuity Monitoring Plug, 3-Wire	20A	125V	L5-20P	Yellow
<b>27W47GCM*</b>	Turnlok® Watertight Ground Continuity Monitoring Connector, 3-Wire	20A	125V	L5-20R	Yellow

\* 20A locking versions have viewing windows, not a transparent housing.

### Watertight Accessories

Catalog Number	Description
<b>PS15WT</b>	Female Watertight Cap, 15/20A Straight Blade & 15A Locking Devices
<b>PS27WT</b>	Female Watertight Cap, 20A Locking Devices
<b>PS29WT</b>	Female Watertight Cap, 30A Locking Devices
<b>PS14WT</b>	Male Watertight Cap, 15/20A Straight Blade & 15A Locking Devices



**NEMA  
5-15P**



**NEMA  
5-15R**



**NEMA  
5-20P**



**NEMA  
5-20R**



**NEMA  
L5-20P**




**NEMA  
L5-20R**

---

## Also available...

- Surge Products
- Turnlok® Locking Devices
- IEC 309 Industrial Products
- Ground Continuity Monitoring (GCM)
- Flexcor® Wire Mesh Grips
- Portable GFCI
- Straight Blade Plugs & Connectors

---

 The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act compliant. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.



**Legrand, North America**  
60 Woodlawn Street  
West Hartford, CT 06110  
1.877.BY.LEGRAND (295.3472)  
[www.legrand.us](http://www.legrand.us)  
570 Applewood Crescent  
Vaughan, Ontario L4K 4B4  
905.738.9195  
[www.legrand.ca](http://www.legrand.ca)

FOLLOW US

