

ES SERIES SHADE SYSTEM

ES/RD DOUBLE SHADES

A complete motorized and banded shading solution

Seamless integration with Wattstopper Lighting Control and Integration Systems



The ES line has a number of universal and modular bracket and fascia options to meet any motorized shading application

DESCRIPTION

The Legrand Shading Systems ES motorized operated roller shade is an extremely flexible shade solution for single, dual, coupled, and oversized motorized shades. The ES series hardware provides a series of different sized brackets and coupler combinations that allow for standalone and coupled shades for straight, curved, or even 90 degree windows for nearly any sized shade. The motors can operate independently with local controls or together with a Wattstopper lighting control system to provide integrated and automated system control with lighting.

OPERATION

ES Double Shades offer universal mount brackets for a variety of motor options and mounting. In addition, using double 4 inch or larger brackets allows for larger double shade configurations. Support for a wide range of coupling options allows multiple double shades to be motorized with a single drive to reduce cost and installation time. All couplers are adjustable allowing installers to adjust shades and light gaps in the field.

All Legrand motorized shades, whether they are DC or AC, are available as a standalone system or as part of a fully automated system using any Legrand lighting control solution.

The added benefits of combining the lighting controls with shading allows for shading and lighting control to operate in parallel to increase energy efficiency and occupant comfort. When combined with Wattstopper Lighting control systems the ES motorized shades offer true shade and lighting automation using astronomic timers and sensors.

APPLICATIONS

The complete ES shade series has motorized shade products for a wide range of applications from Education, Healthcare, to Commercial Office spaces. ES series shades are ideal for projects requiring a complete roller shade solution that encompasses motorized shades that are standalone or coupled. When coupled, a single drive is used to control up to 6 shade bands allowing for significantly lower drive counts on projects when value engineering is required. Dual shades allow for a room darkening shade and solar shade to be mounted in the same window. Both single and dual shades can be coupled with coupling options for windows with a wide range of angles (up to 90 degrees) or even through mullions. There are a number of flexible options for fascia, side channels, and sill rails for room darkening and aesthetics.

NOTE: Number of shade bands varies depending on shade size.

FEATURES

- Available with all motorized roller shade features needed for any commercial project
- Programmable top and bottom limits
- Integration with Wattstopper for control of lighting and shading on a single system.
- BMS compatible using BACnet over IP
- Aluminum tubes: no rust stains on the fabric from high humidity locations
- Mechanically fastened fascia provides increased safety for commercial applications vs clipped or hung fascia
- Double shades can cover windows up to 120 inches wide by 150 inches tall, 130 inches wide by 400 inches tall, or 175 inches wide by 370 inches tall
- Minimal Light gaps ranging from 1" to 1 3/4"
- Side Channels and sill rails available
- Fascia options: choose open roll, or 6 inch fascia options in the color options listed on the following page for single, dual shades and includes back fascia options. Fascia can be joined into various combinations up to 12 inches
- End plate options for fascia combination of 6, 8, 10, and 12 inch fascia. Plates are available in all 9 color options
- Multiple hembar options
- Shade Bands: See Shade Sizing Chart on page 3, Coupling for up to 6 banded shades
- Covered by Legrand Shading systems standard 25 year limited warranty

PROJECT

LOCATION/
TYPE

OPTIONS

Legrand offers a wide range of performance fabrics in different colors, weaves, and price points to make it easy to choose the right shade for your application. Our fabrics are made by leading manufacturers like Phifer and Mermet. We offer numerous environmentally friendly fabrics that are GREENGUARD certified, PVC free, or Cradle-to-Cradle certified. We have fabrics infused with Microban to inhibit the growth of bacteria, mold and mildew that can cause stains, odors and degradation of the fabric. All commercial fabrics are fire rated and carry industry certifications as required by the most stringent of specifications.

Solar Screens - Legrand offers a collection of fabric screens that allow a wide range of view-through and light management options. We offer fabrics with fiberglass and polyester cores, and others coated with PVC or other materials to offer precise light management.


Sustainable Solar Screens - For projects where environmentally conscious requirements are specified. Sustainable options include Cradle to Cradle Certified, PVC-free and 100% recyclable materials incorporated in high quality durable fabrics that still perform as required

Room Darkening Fabrics - A selection of opaque fabrics to block daylight. These materials may be combined with side channels and sill rails to further control light in the space.


Commercial Decorative Fabrics - This collection of commercially compliant fabrics provides aesthetic options for projects where design is an important element.

Fascia & Hembar Finishes*


Gloss White



Beige



Dark Gray



Black




Clear Anodized



Light Bronze



Ceiling White



Charcoal



Dark Bronze




*Side and bottom channel models available, in the color finishes noted for Fascia and Hembar.

Fascia Options

5", 6", and Joined Fascia options, Back Fascia


SHADE OPTIONS

Hembar



NOTE: Concealed and Wrapped & Sealed options available for AC Drive models only


Fabric Drop




Standard Roll

Reverse Roll

Drive Side



Mounting




ES DOUBLE SHADE SYSTEM

The ES Double shade system offers a wide variety of options from compact double brackets to systems using single shade bracket in double configurations. There is a double shade system for shade sized from small to large.

Height and Width limitations and Light Gaps for ES Double Shades

Bracket Style	Max Width (inches)	Max. Height (inches)	Max. Height (ft.)	Fabric Type
One double shade bracket	120	150	12.5	Polyester
	120	150	12.5	Blackout
	120	150	12.5	Fiberglass
Two single shade brackets	175	300	25	Polyester
	175	400	33.3	Blackout
	175	250	29.2	Fiberglass




NOTE: Smaller shades use a single double shade bracket. For larger shades, use two 4" brackets, as shown in the SF-ES6 and SF-ES15 configurations.

DOUBLE SHADE BRACKET DIMENSIONS AND OPTIONS

Slotted mounting holes and universal brackets provide many mounting options with up to ¼ adjustability.

NOTE: For the 4" bracket dimensions, see the ES 5 and 6 inch Series cutsheet.


Bracket Dimensions




Note: Dimensions are identical for all 5 inch brackets, idlers, and couplers.

Standard Motor, Idler, and Coupler Brackets


Star Head Motor Bracket



Idler Bracket



Standard Coupler Bracket





NOTE: Motor and Idler brackets come in left and right versions to provide optimal motor placement options

Up to 1/8" lateral and 1/4" vertical adjustment to adjust for installation and light gaps

ADJUSTABLE COUPLER AND IDLER OPTIONS

Flexible Axle Coupler for Window and Wall Curves less than 45 Degrees.


Offers up to 1/8" lateral and 1/4" vertical adjustment to adjust for installation and light gaps



NOTE: Fascia can be custom mitered to the exact specifications of the window curve.


Adjustable Idler

Allows adjustment of idler depth from 0 to 3/4", in 1/8" increments



Standard 4 Inch Fascia System


Fascia is pressfit, but for a secure connection it is strongly recommended to secure the fascia with self tapping #8, 3/4" screws at both ends and every connection. See assembly drawings on follow page.



Joined Fascia Option

Using 4", 5", or 6" fascia and a joiner allows combinations of fascia pieces for fascia between 8 to 12 inches.

NOTE: There will be a horizontal seam when fascia are joined.



MOUNTING INFORMATION AND DIMENSIONS


The following drawings provide examples of mounting and dimensions for the 4 inch Inch SF-ESxx configurations.

NOTE: Corresponding models of Room Darkening shades (SF-RDxx models) have the same dimensions. Dimensions for the side and bottom channels included at the end of this section. Detailed sectional drawings are also available at <https://legrand.us/shading-systems/commercial-roller-shades/motorized/es-series-motorized-shades/p/es-motorized>

NOTE: Recommended screws for brackets: #8 x 1 1/2" - 4" flat head for wood screws and #8 x 1" - 2 1/2" pan or flat head self tap screws for metal (not included with shade)


SF-ES5

Face mount 5 inch double shade bracket with 6 inch fascia with closure



SF-ES6



One Ceiling mount 4 inch bracket and one Raceway mount 4 inch bracket in pocket with closure





SF-ES15

One Ceiling mount 4 inch bracket and one Raceway mount bracket with two joined 5 inch fascia. Pocket created by Legrand raceway to make an open pocket with no drywall needed


Legrand raceways are designed as a pocketless installation system or to make installation easier in pockets. Contact Legrand Customer Care for assistance in Raceway configuration




SF-RD Models – Similar in configuration to regular ES models, these models add Room Darkening elements (side channels and sill angles)



Side Channel



Sill Rail




NOTE: Works with any hembar option

WIRING AND CONNECTION DIAGRAMS


AC System

AC Drive basic wiring configuration and integration diagram (See AC drive specific cutsheet for more information)



WAGO Connector Dimensions

NOTE: Shades come standard with 6ft long power cable and 3 prong plug. Optional 3 ft, 12 ft, 18 ft, 24 ft lengths with WAGO connectors available



AC Motor Specifications

For AC shade motor system use Somfy ILT or Sonesse 50 RS485 shade motor specifications

ORDERING INFORMATION

Catalog #	Description
ES Shade System Without Blackout Channels	
<input type="checkbox"/> SF-ES5	ES Shade System with Face Mount 5 inch double shade bracket with 6 inch fascia with closure
<input type="checkbox"/> SF-ES6	ES Shade System with Ceiling mount 4 inch bracket and Raceway mount 4 inch bracket in pocket with closure
<input type="checkbox"/> SF-ES15	ES Shade System with Ceiling Mount 4 inch bracket and Raceway mount 4 inch bracket with two joined 5 inch fascia
ES Shade System With Blackout Channels	
<input type="checkbox"/> SF-RD7FM	ES Shade System with Face mount 5 inch double shade bracket with 6 inch fascia with closure, Side and Bottom Channel
<input type="checkbox"/> SF-RD22	ES Shade System with Ceiling and Raceway mount dual 4 inch brackets with two joined fascia with closure, Side and Bottom Channels