


LIGHTING INTEGRATOR 24-RELAY CAPACITY PANEL



Notes:

- ① The maximum length of a local Dataline from each LI Panel with an Automation card is (1500ft) using free topology without a repeater and (8000ft) using linear topology.
- ② Maximum 1000 feet with #20 AWG wire. Additional switches controlling the same zone can be connected in the field or at the relay panel terminals.
- ③ The Network Clock (HCLK8SS) and the Photocell Controller (HPCU8SS) can be located in any panel with enough space on the low voltage din-rail (8-relay panels can hold one device, 24- and 48-relay panels can hold two).

Watt Stopper/Legrand			
800-879-8585			
Title Typical 24-relay Capacity Lighting Integrator Panel Automation Level			
Scale	Drawing#	Date	Rev.
None	60-952	08/26/09	2