

SECTION 26 05 33.16

FLOOR BOXES FOR ELECTRICAL SYSTEMS

PART 1 - GENERAL

1.1 CONDITIONS AND REQUIREMENTS

- A. The General Conditions, Supplementary Conditions, and Division 01 – General Requirements apply.

1.2 SECTION INCLUDES

- A. Resource RFB floor boxes.

1.3 RELATED SECTIONS

Specifier Note: In this article, specify work specified in other sections that is related to work of this section.

- A. Division 26 - Electrical: Electrical systems and components.
- B. Division 27 - Communications: Communications systems and components.
- C. Division 28 - Electronic Safety and Security: Security systems and components.

Specifier Note: The following paragraph is a sample that may be used in this article. Add to or delete from the following as appropriate for the specific project.

- D. Section [xxxxx] – [Section Title]: [Include brief description of work specified in another section that is related to the work of this section.]

1.4 SUBMITTALS

Specifier Note: In this article, specify various types of data to be furnished by the contractor before, during, or after construction. Topics included in this article are: product data, shop drawings, samples, design data, test reports, certificates, manufacturers' instructions, manufacturers' field reports, qualification statements, and closeout submittals.

- A. Submit under provisions of Section [01 33 00] [_____].
- B. Product Data: Submit for floor boxes.

Specifier Note: Delete the following article if not required for a project.

- C. Shop Drawings: For the following electrical system components. Include plans, elevations, sections, details, and attachments to other work.
 - 1. Floor boxes.

1.5 QUALITY ASSURANCE

Specifier Note: In this article, describe qualifications, regulatory requirements, certifications, field samples, mock-ups, and pre-installation meetings.

- A. Manufacturer Qualifications: Firms regularly engaged in manufacture of floor boxes of the types and sizes required, whose products have been in satisfactory use in similar service for not less than 10 years. Provide floor boxes produced by a manufacturer listed in this section.
- B. Electrical Raceways and Components: Comply with requirements of applicable local codes, NEC, UL, and NEMA Standards pertaining to raceways and components. Listed and labeled in accordance with NFPA 70, Article 100.

1.6 DELIVERY, STORAGE AND HANDLING

- A. Deliver floor boxes and fittings in factory labeled packages.
- B. Store and handle in strict compliance with manufacturer's written instructions and recommendations.
- C. Protect from damage due to weather, excessive temperature, and construction operations.

PART 2 - PRODUCTS

2.1 ACCEPTABLE MANUFACTURER

- A. Basis-of-Design Product: The design for floor boxes and fittings is based on the Resource RFB Floor Box Series manufactured by Wiremold/LeGrand, 60 Woodlawn Street, West Hartford, CT 06110; toll-free 800-621-0049, telephone 860-233-6251, fax 860-232-2062; Web Site: www.wiremold.com.
- B. Substitutions will be considered under provisions of Section 01 60 00.

Specifier Note: In the following article, retain only those products that are to be incorporated into the project and delete the others.

2.2 FLOOR BOXES

- A. RFB2 Series Floor Boxes: Manufactured from stamped steel and approved for use on above grade floors. The box shall be 13-1/8" L x 6-1/2" W x 3-7/16" H [333mm x 165mm x 87mm]. Provide the box with two (2) independent wiring compartments that allow capacity for up to two (2) duplex receptacles, communication and audio/video services. The box shall permit tunneling from end power compartment to end power compartment. Provide each of the two (2) compartments with a minimum wiring capacity of 50 cu in [822 ml³]. The box shall include the following number of conduit knockouts: two (2) 1/2-inch [12.7mm], six (6) 3/4-inch [19.1mm], two (2) 1-inch [25mm] and four (4) 1-1/4-inch [32mm]. The box shall be fully adjustable, providing a maximum of 1-3/8-inch [35mm] pre-pour adjustment, and a maximum of 3/4-inch [19.1mm] after-pour adjustment. The box shall include a series of device mounting plates that will accept both duplex power devices as well as plates that will accommodate Ortronics workstation connectivity outlets and modular adapters, the Pass & Seymour Network Wiring System, and other open system devices.

- B. RFB2-SS Series Floor Boxes: Manufactured from stamped steel and approved for use on above grade floors. The box shall be 13-1/8" L x 6-1/2" W x 2-5/8" H [333mm x 165mm x 67mm]. Provide the box with two (2) independent wiring compartments that allow capacity for up to two (2) duplex receptacles, communication and/or audio/video services. The box shall permit tunneling from end power compartment to end power compartment. Provide each of the two (2) compartments with a minimum wiring capacity of 38 cu in [622 ml³]. The box shall contain the following number of conduit knockouts: two (2) 1/2-inch [12.7 mm] and twelve 3/4-inch [19.1 mm]. The box shall be fully adjustable, providing a maximum of 1-3/8-inch [35mm] pre-pour adjustment, and a maximum of 3/4-inch [19.1mm] after-pour adjustment. The box shall include a series of device mounting plates that will accept both duplex power devices as well as plates that will accommodate Ortronics workstation connectivity outlets and modular adapters, the Pass & Seymour Network Wiring System, and other open system devices.
- C. RFB2-OG Series Floor Boxes: Manufactured from stamped steel and painted with a fusion-bonded epoxy designed for use on metal reinforcement bar and related accessories before encapsulation in concrete, and be approved for use on grade and above grade floors. The box shall be 13-1/8" L x 6-1/2" W x 3-7/16" H [333mm x 165mm x 87mm]. Provide the box with two (2) independent wiring compartments that allow capacity for up to two (2) duplex receptacles, communication and/or audio/video services. The box shall permit tunneling from end power compartment to end power compartment. Provide each of the two (2) compartments with a minimum wiring capacity of 50 cu in [822 ml³]. The box shall include the following number of conduit knockouts: two (2) 1/2-inch [12.7mm], six (6) 3/4-inch [19.1mm], two (2) 1-inch [25mm] and four (4) 1-1/4-inch [32mm]. The box shall be fully adjustable, providing a maximum of 1-3/8-inch [35mm] pre-pour adjustment, and a maximum of 3/4-inch [19.1mm] after-pour adjustment. The box shall include a series of device mounting plates that will accept both duplex power devices as well as plates that will accommodate Ortronics workstation connectivity outlets and modular adapters, the Pass & Seymour Network Wiring System, and other open system devices.
- D. RFB4 and RFB4-4DB Series Floor Boxes: Manufactured from stamped steel and approved for use on above grade floors. The box shall be 12-3/4" L x 10" W x 3-7/16" H [324mm x 254mm x 87mm]. Provide the box with four (4) independent wiring compartments that allow capacity for up to four (4) duplex receptacles, communication and/or audio/video services. The RFB4 Series Box shall permit tunneling from end power compartment to end power compartment. The RFB4-4DB Series Box shall permit tunneling from adjacent or opposite compartments. Two (2) of the four (4) compartments shall have a minimum wiring capacity of 16.4 cu in [269cu cm], one (1) compartment shall have a minimum capacity of 32.3 cu in [529cu cm], and one (1) compartment shall have a minimum capacity of 50 cu in [820cu cm]. The box shall include the following number of conduit knockouts: one (1) 1/2-inch [12.7mm], three (3) 1-inch [25mm], six (6) 3/4-inch [19.1mm], and six (6) 1-1/4-inch [32mm]. The box shall be fully adjustable, providing a maximum of 1-7/8-inch [47.7mm] pre-pour adjustment, and a maximum of 3/4-inch [19.1mm] after-pour adjustment. The box shall include a series of device mounting plates that will accept both duplex power devices as well as plates that will accommodate Ortronics® workstation connectivity outlets and modular adapters, the Pass & Seymour Network Wiring System, and other open system devices.
- E. RFB4-CI-1 Series Floor Boxes: Manufactured from cast-iron and approved for use on grade and above grade floors. The box shall be 14-1/2" L x 11-7/8" W x 3-7/16" H [368mm x 302mm x 87mm]. Provide the box with four (4) independent wiring compartments that allow capacity for up to four (4) duplex receptacles and/or communication services. The box shall permit tunneling from adjacent or opposite compartments. Two (2) of the four (4) compartments shall

have a minimum wiring capacity of 27 cu in [443cu cm], and two (2) compartments shall have a minimum wiring capacity of 36 cu in [590cu cm]. The box shall include the following number of conduit hubs: four (4) 1-inch [25mm] and four (4) 1-1/4-inch [32mm]. The box shall be fully adjustable, providing a maximum of 1-7/8-inch [48mm] pre-pour adjustment, and a maximum of 3/4-inch [19.1mm] after-pour adjustment. The box shall include a series of device mounting plates that will accept both duplex power devices as well as plates that will accommodate Ortronics® workstation connectivity outlets and modular adapters, and other open system devices.

- F. RFB4-SS Series Floor Boxes: Manufactured from stamped-steel and approved for use on above grade floors. The box shall be 13-5/8" L x 10" W x 2-7/16" H [346mm x 254mm x 62mm]. Provide the box with four (4) independent wiring compartments that allow capacity for up to four (4) duplex receptacles, communication and/or audio/video services. The box shall permit feed through tunneling from adjacent compartments. Two (2) of the four (4) compartments shall have a minimum wiring capacity of 15.7 cu in [257cu cm], and two (2) compartments shall have a minimum wiring capacity of 31.2 cu in [511cu cm]. The box shall contain the following number of conduit knockouts: two (2) 1/2-inch [12.7mm], six (6) 3/4-inch [19.1mm], and eight (8) 1-inch [25mm]. The box shall be fully adjustable, providing a maximum of 1-7/8-inch [48mm] pre-pour adjustment, and a maximum of 3/4-inch [19.1mm] after-pour adjustment. The box shall include a series of device mounting plates that will accept both duplex power devices as well as plates that will accommodate Ortronics® workstation connectivity outlets and modular adapters, and other open system devices.
- G. RFB6 Series Floor Boxes: Manufactured from stamped steel and approved for use on above grade floors. The box shall be 13-1/8" L x 12-1/2" W x 3-1/4" H [333mm x 317mm x 83mm]. Provide the box with six (6) independent wiring compartments that allow capacity for up to six (6) duplex receptacles, communication and/or audio/video services. The box shall permit feed through tunneling from adjacent compartments. Two (2) of the six (6) compartments shall have a minimum wiring capacity of 23 cu in [376cu cm], and four (4) compartments shall have a minimum wiring capacity of 52cu in [850cu cm]. The box shall contain the following number of conduit knockouts: twelve 3/4-inch [19.1mm], four (4) 1-inch [25mm], and twelve 1-1/4-inch [32mm]. The box shall be fully adjustable, providing a maximum of 1-3/8-inch [35mm] pre-pour adjustment, and a maximum of 3/4-inch [19.1mm] after-pour adjustment. The box shall include a series of device mounting plates that will accept both duplex power devices as well as plates that will accommodate Ortronics workstation connectivity outlets and modular adapters, the Pass & Seymour Network Wiring System, and other open system devices.
- H. RFB6-OG Series Floor Boxes: Manufactured from stamped steel and painted with a fusion-bonded epoxy designed for use on metal reinforcement bar and related accessories before encapsulation in concrete, and approved for use on grade and above grade floors. The box shall be 13-1/8" L x 12-1/2" W x 3-1/4" H [333mm x 317mm x 83mm]. Provide the box with six (6) independent wiring compartments that allow capacity for up to six (6) duplex receptacles, communication and/or audio/video services. The box shall permit feed through tunneling from adjacent compartments. Two (2) of the six (6) compartments shall have a minimum wiring capacity of 23 cu in [376cu cm], and four (4) compartments shall have a minimum wiring capacity of 52cu in [850cu cm]. The box shall contain the following number of conduit knockouts: twelve 3/4-inch [19.1mm], four (4) 1-inch [25mm], and twelve 1-1/4-inch [32mm]. The box shall be fully adjustable, providing a maximum of 1-3/8-inch [35mm] pre-pour adjustment, and a maximum of 3/4-inch [19.1mm] after-pour adjustment. The box shall include a series of device mounting plates that will accept both duplex power devices as well as plates

that will accommodate Ortronics workstation connectivity outlets and modular adapters, the Pass & Seymour Network Wiring System, and other open system devices.

- I. RFB6E Series Floor Boxes: Manufactured from stamped steel and approved for use on above grade floors. The box shall be 13-1/8" L x 12-1/2" W x 4" H [333mm x 317mm x 102mm]. Provide the box with six (6) independent wiring compartments that allow capacity for up to six (6) duplex receptacles, communication and/or audio/video services. The box shall permit feed through tunneling from adjacent compartments through 1-1/4-inch grommet openings. Two (2) of the six (6) compartments shall have a minimum wiring capacity of 23 cu in [376cu cm], and four (4) compartments shall have a minimum wiring capacity of 52cu in [850cu cm]. The box shall contain the following number of conduit knockouts: twelve 3/4-inch [19.1mm], four (4) 1-inch [25mm], and twelve 1-1/4-inch [32mm]. The box shall be fully adjustable, providing a maximum of 1-3/8-inch [35mm] pre-pour adjustment, and a maximum of 3/4-inch [19.1mm] after-pour adjustment. The box shall include a series of device mounting plates that will accept both duplex power devices as well as plates that will accommodate Ortronics workstation connectivity outlets and modular adapters, and other open system devices.
- J. RFB6E-OG Series Floor Boxes: Manufactured from stamped steel and painted with a fusion-bonded epoxy designed for use on metal reinforcement bar and related accessories before encapsulation in concrete, and approved for use on grade and above grade floors. The box shall be 13-1/8" L x 12-1/2" W x 4" H [333mm x 317mm x 102mm]. Provide the box with six (6) independent wiring compartments that allow capacity for up to six (6) duplex receptacles, communication and/or audio/video services. The box shall permit feed through tunneling from adjacent compartments. Two (2) of the six (6) compartments shall have a minimum wiring capacity of 23 cu in [376cu cm], and four (4) compartments shall have a minimum wiring capacity of 52cu in [850cu cm]. The box shall contain the following number of conduit knockouts: twelve 3/4-inch [19.1mm], four (4) 1-inch [25mm], and twelve 1-1/4-inch [32mm]. The box shall be fully adjustable, providing a maximum of 1-3/8-inch [35mm] pre-pour adjustment, and a maximum of 3/4-inch [19.1mm] after-pour adjustment. The box shall include a series of device mounting plates that will accept both duplex power devices as well as plates that will accommodate Ortronics workstation connectivity outlets and modular adapters, and other open system devices.

2.3 ACTIVATION COVERS

- A. FloorPort FPCT, FPBT, and FPFCT Series Covers: Manufactured of die-cast aluminum or die-cast zinc, and available in brushed aluminum finish and powder-coated paint finishes (black, gray, bronze, nickel and brass). Activation covers shall be available in flanged and flangeless versions. Covers shall be available with options for tile or carpet inserts, or flush covers. The cover's hinge shall allow for the cover to open 180 degrees. The furniture feed covers shall come equipped with one (1) 1-inch trade size screw plug opening and one (1) combination 1-1/4-inch and 2-inch trade size screw plug.
 - 1. Flanged covers shall be 7-3/4" L x 6-9/16" W [197mm x 167mm].
 - 2. Flangeless covers shall be 6-3/4" L x 5-9/16" W [171mm x 142mm].
- B. 8CT Series Covers: Manufactured of die-cast aluminum alloy and available in powder-coated gray, black, brass, nickel or bronze finish. The covers shall be available in carpet and tile versions. Provide covers with two (2) gaskets (one (1) for carpet and one (1) for tile) to go under the trim flange to maintain scrub water tightness. The activation cover shall be 9-1/4-inch [235mm] in diameter. The carpet covers shall be surface mounted and the tile covers

shall be flush with the finished floor covering. The cover shall have spring loaded slides to allow cables to egress out of the unit and maintain as small an egress opening as possible.

- C. The covers shall have been evaluated by UL to meet the applicable U.S. and Canadian safety standards for scrub water exclusion when used on tile, terrazzo, wood, and carpet covered floors.

2.4 COMMUNICATION MODULES MOUNTING ACCESSORIES

- A. The floor box manufacturer shall provide a complete line of faceplates and bezels to facilitate mounting of UTP, STP (150 ohm), fiber optic, coaxial, and communication devices. The box shall provide a series of device mounting plates that will accommodate Ortronics workstation connectivity outlets and modular adapters, the Pass and Seymour Network Wiring System, and other open system devices.

PART 3 - EXECUTION

3.1 EXAMINATION

Specifier Note: Delete either of the options in the paragraph below to suit project requirements.

- A. Examine conditions under which boxes and fittings are to be installed and substrate that will support boxes. Notify the [Architect/Engineer] [Construction Manager] in writing of conditions detrimental to proper completion of the work. Do not proceed with work until unsatisfactory conditions have been corrected.

3.2 INSTALLATION

- A. Strictly comply with manufacturer's installation instructions and recommendations and approved shop drawings. Coordinate installation with adjacent work to ensure proper clearances and to prevent electrical hazards.
- B. Mechanical Security: Raceway systems shall be mechanically continuous and connected to all electrical outlets, boxes, device mounting brackets, and cabinets, in accordance with manufacturer's installation sheets.
- C. Accessories: Provide accessories as required for a complete installation, including insulated bushings and inserts where required by manufacturer.
- D. Unused Openings: Close unused box openings using manufacturer's recommended accessories.
- E. Provide a minimum concrete pour depth of 3-7/16-inch [87mm] plus 1/16-inch [1.6mm] above the top of the box for the RFB4, RFB4-4DB, RFB2, and the RFB2-OG Series Boxes; 2-7/16-inch [62mm] plus 1/16-inch [1.6mm] for the RFB4-SS and RFB2-SS Series Boxes; and 3-7/16-inch [87mm] plus 13/16-inch [21mm] above the top of the box for the RFB4-CI-1, RFB6, RFB6-OG, RFB6E and RFB6E-OG Boxes. Provide the box with four (4) locations to accommodate leveling for pre-concrete pour adjustment and include four (4) leveling screws for the pre-pour adjustment.

3.3 CLEANING AND PROTECTION

- A. Clean exposed surfaces using non-abrasive materials and methods recommended by manufacturer.
- B. Protect boxes and fittings until acceptance.

END OF SECTION

© 2009 Wiremold/Legrand. All Rights Reserved.
A copyright license to reproduce this specification is hereby granted
to non-manufacturing engineers, architects and specification writers.
New 12/09