



## LCD CONSOLE WITH LYRIQ, WHITE

HA5009-WH | [On-Q](#)

### FEATURES & BENEFITS

This 7" LCD Console features a simple graphic user interface that allows control of camera, multi-room audio, intercom, lighting and messaging functions when coupled with the Integration Module of the Unity Home System. The console mounts in a standard triple gang box and installs easily via Cat 5 wiring with convenient RJ45 connections.

This LCD features additional connections for LyriQ that turn it into a volume control when used as part of the Unity Home System.

- Mounts in a standard triple gang box and installs easily via Cat 5 wiring with convenient RJ45 connections.
- 7" LCD screen with a simple push button interface to select desired input.
- Controllable through an On-Q IR remote control.
- Attractive design complements the home and matches other On-Q devices in the Studio design.
- Up to four video feeds available with on-board sequencing of camera images.
- Additional connections for LyriQ to turn screen into volume control.
- Integration module required.

### SPECIFICATIONS

#### GENERAL INFO

Discontinued: Yes  
Color: White

#### DIMENSIONS

Overall Dimensions (US): 7.00"H x 7.25"W x 3.5"D

#### CORD INFORMATION

Pinning: LCD Out

1. Left Audio (PreGND) Audio Pre-Ground
2. Left Audio Input Audio Signal (line level analog)
3. Right Audio (PreGND) Audio Pre-Ground
4. IR (IR TX) Output IR Command (analog 12V max signal)
5. Status (IR RX) Input IR Command

(analog 12V max signal)

6. Right Audio Input Audio Signal (line level analog)

7. Ground Power Ground

8. Power (+24VDC) +24Vdc Power Input lyriQ Out

1. Left Audio (PreGND) Audio Pre-Ground

2. Left Audio Input Audio Signal (line level analog)

3. Right Audio (PreGND) Audio Pre-Ground

4. IR (IR TX) Output IR Command (analog 12V max signal)

5. Status (IR RX) Input IR Command (analog 12V max signal)

6. Right Audio Input Audio Signal (line level analog)

7. Ground Power Ground

8. Power (+24VDC) +24Vdc Power Input

#### TECHNICAL INFORMATION

Cat5 Cable Rating: Cat 5e UTP, 4 Pair Solid Conductor (24 AWG)

Frequency Response: 20 - 20,000Hz  $\pm$  2dB with lyriQ Add-On Board

IR Range On Axis: 25ft Max

IR Receive Frequency: 10 kHz – 110 kHz

Mounting: protruded 6/8" off Wall Surface

Output And Line Out Connection: 14-28 AWG Springcon® Terminal Block with lyriQ Add-On Board

Output Impedance: 8  $\Omega$  (1 pair of speakers) with lyriQ Add-On Board

Power Requirements: +24Vdc, +/-1.5Vdc, 0.75 A max; +24Vdc  $\pm$  6Vdc, 500mA average with lyriQ Add-On Board

QLink Video Ports: RJ-45

Speaker Impedance Load: 4 Ohm Max with lyriQ Add-On Board