



## 20" PLASTIC ENCLOSURE, ONLY

ENP2080 | [On-Q](#)

### FEATURES & BENEFITS

Constructed with a robust, wireless transparent ABS plastic material, this lightweight enclosure is designed to integrate wireless devices into traditional structured wiring installations.

The enclosure mounts easily for both surface and recessed applications, and hinged door is equipped with extra venting along the vertical plane for superior heat dissipation.

Hinged cover (ENP2060) purchased separately to complete installation during trim-out phase. [Click here](#) to learn more about the unique features that will save you time and simplify installation.



- Made with ABS plastic, the enclosure is designed to integrate wireless devices without interference.
- Universal mounting grid maximizes compatibility with 3rd party products without additional brackets.
- Installs into a single stud bay and staggered mounting tabs allow multiple enclosures to mount in adjacent stud bays.
- Tapered design allows enclosures to stack for efficient transportation and warehousing.
- Top surface includes five 2" knockouts; rubber grommets available for purchase (AC1034).
- Bottom surface includes two AC receptacle box knockouts and two 1 1/4" knockouts.
- UL listed.

### SPECIFICATIONS

#### GENERAL INFO

Color: White (Paintable)\*  
Type: Enclosure

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: UL 60950-1 & CAN/CSA C22.2 No. 60950-01-07 Information Technology Equipment, Including

Electrical Business Equipment

CSA Standard: Yes

UL Listing No: UL 2416, Audio/Video, Information and Communication Technology Equipment Cabinet, Enclosure and Rack Systems

UL Standard: Yes

## **CONSTRUCTION INFORMATION**

Material 1: ABS Plastic

## **DIMENSIONS**

Depth (Metric): 105.9mm

Depth (US): 4.17"

Height (Metric): 530.9mm

Height (US): 20.9"

Width (Metric): 363.5"

Width (US): 17.1"

Primary Packaging Weight (Metric): 2.04kg

Product Weight (Metric): 1.13 kg

Product Weight (US): 2.5 lbs

## **TECHNICAL INFORMATION**

Material: ABS Plastic

Operating Temperature (Celsius): 0°C to 50°C