
2-WAY DIGITAL CABLE SPLITTER W/ COAX NETWORK SUPPORT

VM2202-V1 | [On-Q](#)

FEATURES & BENEFITS

This professional-grade digital cable splitter distributes HDTV Antenna/Digital Cable and coax data network signals to two devices. Ideal for MoCA-capable networks.

- Exceeds the performance standards set by major cable providers
- Compatible with existing and future networks such as MoCA, VoIP, and DOCSIS 3.0
- 6kV Surge Protection on all ports
- Coax networking adapters and splitters are not compatible with satellite television systems

SPECIFICATIONS

GENERAL INFO

Cable Type: Coaxial

Color: Black

Connection Type: ANSI/SCTE 01 Compliant ECT F-port

Type: Signal Splitter

Surge Protected: 6 kV ring wave surges per IEEE specification C62.41 Category A3

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

UN SPSC: 32101529

DIMENSIONS

Depth (Metric): 16.3 mm

Depth (US): 0.64"

Length (Metric): 2.3"

Length (US): 59.6 mm

Width (Metric): 45.1 mm

Width (US): 1.8 in

TECHNICAL INFORMATION

Frequency: 5 MHz - 1525 MHz

OhmValue: 75 Ohm Nominal impedance

Operating Temperature (Celsius): -40°C to 60°C

Supported Standards: Exceeds ANSI/SCTE 143 specifications for corrosion, 1000 hours

Typical Insertion Loss:

Freq(MHz)	Typ(dB)
5 - 200	3.3
201 - 550	3.5
551 - 750	3.7
751 - 1002	3.8
1125 - 1325	6.0
1326 - 1525	9.0

Typical Return Loss:

Input:

Freq(MHz)	Typical
5 - 14	25 dB
15 - 200	30 dB
201 - 550	22 dB
551 - 1002	20 dB

Output:

Freq(MHz)	Typical
5 - 14	28 dB
15 - 40	35 dB
41 - 200	30 dB
201 - 550	25 dB
551 - 1002	20 dB