



## MM20 CHANNEL RACK, 24"D CHANNEL, 8'H, 51 RU, TAPPED #12-24

OR-MM20824-X | [Ortronics](#)

### FEATURES & BENEFITS

Mighty Mo 20 channel racks are designed to provide greater flexibility and optimum efficiency to any size network. The top trough with built-in waterfall provides bend radius control and efficient patch cable routing. Honeycomb side rails on all depth channel racks provide the ultimate in distribution cable management. On 16-1/4" and deeper channel racks, honeycomb side rails and airflow baffles combine to create a patented system that manages intake and exhaust air from side vented equipment.

Note: Static capacity 2,000 lbs. Assembly required. Replace the "X" tail code with "B" for black or "W" for white.



**PRODUCT**  
ENVIRONMENTAL PROFILE

- **Patented channel construction:** Protects the performance of your horizontal cabling better than any other type of racking solution. Hex pattern on all rack sizes simplify cable routing.
- **Honeycomb side rails designed to maximize the airflow of network equipment:** Combined with baffles, manages intake and exhaust air creating cold aisle/hot aisle distribution from side vented equipment.
- **Open channels top and bottom:** Allows floor and ceiling access for horizontal distribution cables.
- **EIA hole pattern front and rear of channel:** Supports equipment shelves and heavy electronics while power strips and other accessories can be mounted to the rear rail without using additional rack space.
- **High density racking solution:** 7 foot has 45 rack units front and rear.
- **Choice of vertical management:** A solution for every application; vertical cable management cage with individual rack unit fingers and hinged slam latch door, vertical cage with individual rack unit fingers and snap on covers, vertical cage with hinged latches, and individual cable management rings.
- **Built-in top trough with waterfalls:** Gives bend radius control and cable routing.
- **Can be assembled as a 19" or 23" rack:** No additional hardware required; no need to stock two sizes of racks.
- **Speed nuts included:** Increases speed and ease of assembly, while adding extra strength to your rack-- Speednut eliminates the need for a second wrench.
- **Rack includes hardware kit, two packages of hook and loop D-style straps and 50 #12-24 equipment mounting screws:** Do not have to purchase as separate items; money saving.

## SPECIFICATIONS

### GENERAL INFO

Color: (B)lack or (W)hite  
Product Series: Mighty Mo 20  
Type: Cable Management Racks  
Component Type: Channel Rack

### ASSEMBLY/INSTALLATION INFORMATION

Assembly Required: Yes  
Mounting Hardware Included: Yes

### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

### CONSTRUCTION INFORMATION

Component 1: Channel Rack

### DIMENSIONS

Capacity Weight (US): 2000 lbs  
Depth (US): 34  
Diameter (Metric):  
Height (Metric): 2.4892 m  
Height (US): 98"  
Length (Metric):  
Width (Metric): 603.25 mm  
Width (US): 23.75"  
Height: 98"  
Rack Units: 51

### TECHNICAL INFORMATION

Static Load Capacity: 2,000 lb  
Patent No: 8,130,494 and 8,256,181

### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA  
Buy American Act Status: Buy American Act Compliant

