



## PLUGTAIL® SPEC-GRADE TAMPER-RESISTANT 20A SELF-TEST NIGHT LIGHT/GFCI, WHITE

PT2097NTLTRW | [Pass & Seymour](#)

### FEATURES & BENEFITS

The fastest-installing GFCI ever now conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the indicator light flashes to signal that the GFCI should be replaced. It also has our proven SafeLock™ Protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected.

For detailed PlugTail® information, visit our [PlugTail Headquarters](#).

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles page](#).

For detailed GFCI receptacle information, visit our [GFCI Headquarters](#).



- Protects children: patented shutter system helps prevent improper insertion of foreign objects.
- Meets National Electrical Code® Tamper-Resistant requirements.
- Sealed night light with high-impact-resistant Lexan® lens prevents tampering.
- Night light uses cooler LED illumination.
- Energy-efficient LED has average 20-year life expectancy, eliminating bulb replacement.
- Photocell turns night light ON in dark, OFF in daylight.
- Faster, more reliable installation.
- No exposed terminals create a finger-safe application before, during, and after installation.
- Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections to PlugTail® Connector.
- GFCI works with existing 3-wire PlugTail Connectors creating a non-feed-thru application for facility owners.
- Conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the indicator light flashes to signal that the GFCI should be replaced. It also has our proven SafeLock protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected.
- Thinner than competitors' GFCI Receptacles: leaves more room for wires in the box.
- Auto-Ground clip assures a positive ground to metal box.
- Meets 2015 UL requirements.
- Exceeds UL 943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- FSUL Listed (Federal Specification WC596).

- Trip indicator light (red LED).
  - 10kA short circuit rating.
  - Mounting screws are shipped captive in the device and wall plate for easier installation.
  - High-impact-resistant thermoplastic construction.
  - Zinc-plated steel mounting strap.
  - Button colors match the device face.
  - Dual-direction test and reset buttons.
  - Class A rated GFCI.
  - Supplied with matching TP wall plate.
  - Tri-drive screws.
  - Supply Voltage: 125VAC, 60 Hz
  - Supply Voltage Range: 102-132 VAC
  - Trip Threshold: 5 +/- 1 mA
  - Trip Time: 0.025 sec., nominal per UL Standard
- 

## SPECIFICATIONS

### GENERAL INFO

Color: White

Special Features: Tamper-Resistant

### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listed: No

cULus: Yes

Federal Spec: Yes

UL Standard: UL498

### TECHNICAL INFORMATION

Amps: 20A

NEMA Configuration Number: 5-20R

Volts: 125

### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA