

---

## FIXED DUAL SHELF, VENTED, 1.56"H X 17.50" W X 20.50"D

OR-ESV-19-SDR1520F | [Ortronics](#)



---

### FEATURES & BENEFITS

Dual Fixed Shelf, Vented, 1.56"H x 17.50" W x 20.50"D, center load rating: 125 lbs., distributed load rating: 300 lbs.



- Mounts to all Ortronics adjustable dual equipment racks
- Heavy-duty for high load bearing capacity
- Bottom brackets adjust to rack depth
- Easy to add and remove deep equipment
- Fully usable surface area to accommodate servers
- Air flow slots ensure equipment is kept cool
- 12-24 cage nuts and screws included
- Steel construction with black finish

---

### SPECIFICATIONS

#### GENERAL INFO

Type: Shelves  
Features: Vented

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

#### CONSTRUCTION INFORMATION

Component 1: Shelf  
Finish Plating 1: Powder coat black  
Material 1: 16 GA (.0598) CRS

#### DIMENSIONS

Capacity Weight (US): center load rating: 125 lbs, distributed load rating: 300 lbs  
Depth (Metric): 521 mm  
Depth (US): 20.50"  
Height (Metric): 40 mm  
Height (US): 1.56"  
Width (Metric): 445 mm  
Width (US): 17.50"  
Product Weight (US): 13.0 lbs  
Rack Units: 1

**BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: UNITED STATES OF AMERICA  
Buy American Act Status: Buy American Act Compliant

